

3M™ Metal-out Static Shielding Bag SCC 1500

Static Shielding Bag - Metal-out

3M SCC 1500 metal-out static shielding bags are approved by major electronics manufacturers for use worldwide. Our transparent, metallized static shield bag structure is designed to provide a static safe environment for sensitive electronic devices. This bag also provides low charge retention and rapid static decay. Bags are lot coded for QC traceability. These bags are tested to meet or exceed certain electrical and physical requirements of ANSI/ESD S541, EIA 625, and to be ANSI/ESD S20.20 program compliant.

Specifications

Physical Properties:

Physical Properties:	Typical Values	Test Method*
Thickness	3 mils**	MIL-STD-3010 1003
Tensile Strength	7700 PSI	ASTM D882
Seam Strength	>10 lbs	ASTM D882
Heat Sealing Conditions:		
Temperature	300°F - 400°F	
Time	0.6 - 4.5 seconds	
Pressure	30 - 70 PSI	

Electrical Properties:

Surface Resistivity / Resistance	ASTM D257	or ANSI/ESD STM11.11
Interior	<10 ¹² ohms/square	or <10 ¹¹ ohms
Exterior	<10 ¹² ohms/square	or <10 ¹¹ ohms
Metal	100 ohms	
Charge Retention	<100 volts	CPM
Static Shielding	< 30 volts	EIA 541
Static Shielding	< 10 nJ	ANSI/ESD STM11.31
Static Decay	< 2 seconds	MIL-STD-3010 4046
Silicone or Amine Content	Not detected	FTIR

** tolerance +/-15%

See 3M Data Sheets for these related items:

- Humidity Indicator Cards (HIC's)
- Desiccant
- Vacuum Sealers

Open Top




ZipTop Reclosable



Material Structure

3M SCC 1500 flat and ZipTop static shielding bags are manufactured using a proprietary top coating. The top coating and metal layer provide low charge retention and Faraday Effect shielding of an Electrostatic Discharge (ESD) with the associated electrostatic fields. Polyester dielectric stops the current from ESD. Tribocharging is minimized by the specially processed polyethylene.



Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

*This product is not on the Qualified Product Listing under the Defense Standardization Program.

P R O D U C T D A T A S H E E T

SCC 1500 Metal-out Static Shielding Bag

PRODUCT	ITEM NUMBER	DATASHEET
STATIC SHIELDING BAG, OPEN TOP AND ZIPTOP	150(W")(L")	1101-B
		98-0799-1066-1

3M Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726-9000
US and Canada: 866-722-3736
Fax: 866-722-3735
Int'l: 919-718-0000; Fax: 919-774-8174
email: 3Mstaticinfo@mmm.com; www.3Mstatic.com


3M is a trademark of 3M Company.
All other trademarks herein are the property of their respective owners.



3M™ Metal-out Static Shielding Bag SCC 1500

Static Shielding Bag - open top

W"x L"	P/N	W"x L"	P/N	W"x L"	P/N
3 x 5	15035			12 x 16	1501216
4 x 6	15046	8 x 12	150812	12 x 18	1501218
5 x 8	15058	9 x 12	150912	14 x 18	1501418
6 x 8	15068	10 x 12	1501012	15 x 18	1501518
6 x 10	150610	10 x 14	1501014	16 x 24	1501624
6 x 30	150630	10 x 24	1501024	18 x 18	1501818
7 x 15	150715	11 x 15	1501115	18 x 24	1501824



3M™ Metal-out Static Shielding Bag SCC 1500

Static Shielding Bag - ZipTop Reclosable

W"x L"	P/N	W" x L"	P/N	W" x L"	P/N
3 x 5	150Z35	5 x 8	150Z58	8 x 10	150Z810
4 x 4	150Z44	6 x 8	150Z68	10 x 12	150Z1012
4 x 6	150Z46	6 x 10	150Z610	12 x 18	150Z1218

- All standard sizes in-stock/same day shipment.
- Width is measured from inside seam to inside seam.
- Length is measured from the top edge to the bottom fold.
- Opening is in the "width" dimension.
- Custom bag sizes, custom printing, and custom hot stamping are available.
- Most sizes are packed 100 per case.
Small sizes are packed 1000 or 500 per case.

P R O D U C T D A T A S H E E T

SCC 1500 Metal-out Static Shielding Bag

PRODUCT
STATIC SHIELDING BAG, OPEN TOP AND ZIPTOP

ITEM NUMBER
150(W")(L")

DATASHEET
1101-B
98-0799-1066-1

3M Electronic Solutions Division
6801 River Place Blvd
Austin, TX 78726-9000
US and Canada: 866-722-3736
Fax: 866-722-3735
Int'l: 919-718-0000; Fax: 919-774-8174
email: 3Mstaticinfo@mmm.com; www.3Mstatic.com

3M is a trademark of 3M Company.
All other trademarks herein are the property
of their respective owners.



© 3M 2012. All rights reserved.