

OGA DIAGONAL: 13.16 [334.34]  
 VA DIAGONAL: 12.39 [314.63]  
 PA DIAGONAL: 11.70 [297.08]



TOP LEVEL NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PRODUCT SPEC
98-0003-3138-3	FFC	8.00" [203.20]	AG500	36235
98-0003-3139-1	SER	8.00" [203.20]	AG500	36235
98-0003-3140-9	USB R	8.00" [203.20]	AG500	36235

ESD CLAMSHELL CASE IS USED WITH ALL USB AND SER TERMINATIONS.



**(SER)**  
 EXII-7720SC  
 98-0003-2217-6  
 SERIAL CONTROLLER  
 SOLDER SIDE

**(USB R)**  
 EXII-7760UC  
 98-0003-2814-0  
 USB CONTROLLER  
 SOLDER SIDE



NOTES:

- WEIGHT OF GLASS IN GRAMS: 968±10%
- 5 PIN AMP CONNECTOR LATCH STYLE HOUSING P/N: 487526-4 TIN CONTACTS P/N: 2-487406-4 HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LR
2	LL
3	SHLD
4	UL
5	UR

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	± .03 [.76]
.XX	±.015 [.38]
.XXX	±.01 [.25]
ANGLES	±1°
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE	1 = 1

**3M** 3M TOUCH SYSTEMS  
 METHUEN, MA  
 USA  
 © COPYRIGHT 2004  
 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.

REV	CHANGE NOTICE	DATE	DRW
03	REVISE PER CO 030448	5/09	SB
02	REVISE PER CO 030178	3/09	AH
01	INITIAL RELEASE PER CO 029886	1/09	MTD

TITLE  
**MARKETING DRAWING**  
**SCT76NN 12.39"**

DRAWN	MTD	1/13/09
SIZE	C	DOCUMENT NO. 36469-MKT
SHEET	1 OF 1	REV 03