

6

5

4

3

2



1

APPROVED: _____


DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE / NON-RETURNABLE


Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/18	



Washer:
Brass, Gold



Nut:
Brass, Gold



O-Ring
ø6/2T, Black



H

SPECIFICATIONS:

Connector:

P1= I-PEX Connector, Gold plated

P2= SMA Jack (JR), Straight, Male pin, Gold plated

Cable:

ø1.37mm Coaxial Cable, Color: Black

Electrical:

Impedance: 50 ohms

Frequency range: DC-6 GHz

Electrical Test:

All Assemblies must be 100% Tested for Shorts, Open, Continuity, and Physical Appearance.

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

ADAM TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

APPROVALS		DATE
DRAWN	AY	11/16/18
CHECKED	AC	11/16/18
APPROVED		

TITLE CUSTOM CABLE ASSEMBLY, IPEX PLUG TO SMA S/T JACK (JR) WITH OD 1.37MM CABLE		
SIZE X	PART NO. CA#DKCA0-152L1-AL10-O	REV. -
REF: S00291T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1