

6

5

4

3

2


1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

CUSTOM CABLE ASSEMBLIES ARE NON-CANCELLABLE / NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/18	



**SPECIFICATIONS:**

**Connector:**

P1= MCX Plug, Male Pin, Straight, Gold plated

P2= MCX Plug, Male Pin, Right Angle, Gold plated

**Cable:**

RG178 Cable

**Electrical:**

Impedance: 50 ohms

Frequency range: DC-6 GHz

**Electrical Test:**

All Assemblies must be 100% Tested for Shorts, Open, Continuity, and Physical Appearance.

**Environmental:**

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES

.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

**ADAM TECH**  
**INTERCONNECTS**  
 909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

TITLE  
CUSTOM CABLE ASSEMBLY, MCX STR PLUG TO MCX R/A PLUG WITH RG178 CABLE

APPROVALS		DATE
DRAWN	AY	10/18/18
CHECKED	RC1	10/18/18
APPROVED		

SIZE	PART NO.	REV.
X	CA#DKCA1-152L3-DPDRP-12	-
REF: S00291T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1