

AMPHENOL RF PART NUMBER

031-2374

TNC Straight Crimp Jack for RG-58C, RG-141A, 50 Ohm

Amphenol® RF



PRODUCT IMAGE
COMING SOON

PRODUCT OVERVIEW

RF Connector, TNC Straight Crimp Jack for RG-58C, RG-141A, 50 Ohm

Product Type	Connectors
Product Series	TNC
Status	Active

PRODUCT SPECIFICATIONS

Gender	Jack
Orientation	Straight
Termination Style	Cable - Crimp
Impedance (Ohms)	50
Body Finish	Nickel
Body Material	Brass
Contact Finish	Gold
Contact Material	Phosphor Bronze
Contact Termination Style	Crimp
Insulator Material	PTFE
Cable Group	C
Cable Type	Belden 9907, Belden B7806A, LMR-195, RG-141, RG-303, RG-58, RG-58A, RG-58B, RG-58C
Crimp Tool	CTL-5
Coupling Mechanism	Threaded
Max Frequency (GHz)	11
Polarity	Standard

Thread Direction	Standard
Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500
Weight (Grams)	13.154

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------