

AMPHENOL RF PART NUMBER

082-B0202-2218

N-Type Straight Clamp Jack for RG-188, Panel Mount, 75 Ohm

Amphenol® RF



PRODUCT IMAGE
COMING SOON

PRODUCT OVERVIEW

RF Connector, N-Type Straight Clamp Jack for RG-188, Panel Mount, 75 Ohm

Product Type	Connectors
Product Series	N-Type
Status	Active

PRODUCT SPECIFICATIONS

Gender	Jack
Orientation	Straight
Termination Style	Cable - Clamp
Impedance (Ohms)	50
Body Finish	Passivated
Body Material	Stainless Steel
Contact Finish	Gold
Contact Material	Beryllium Copper
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	B
Cable Type	LMR-100, M17/119-RG174, RG-174, RG-188, RG-188A, RG-316
Coupling Mechanism	Threaded
Mounting Feature	4-Hole Flange
Max Frequency (GHz)	11
Polarity	Standard

Thread Direction	Standard
Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------