

Office

JD-0400EU-2



Actual product may vary from the image shown

Secure Data Transmission and A Reliable Power Supply!

The wireless desktop set JD-0400EU-2 combines guaranteed secure data transmission and an advanced energy supply. It is meant for top professional requirements and security both at home and in the office.

Facts & Features

- Data transmission using 128-bit encryption, complying to Advanced Encryption Standard (AES)
- USB cable charging function for both keyboard & mouse – even when in use
- High-quality, pre-charged NiMH batteries with a very low self-discharge
- 3-button mouse: infrared sensor and adjustable resolution (1,000/2,000 dpi) with ergonomic side panels
- Interference-free wireless connection: Maximum wireless range (up to 10 meters) using 2.4 GHz wireless technology

Technical Data

Housing and Key Color:

Black

Weight (product):

Approx. 883 g/1.94 lbs (keyboard with battery), approx. 145 g/ .31 lbs (mouse with battery), approx. 6 g/ .01 lbs (receiver)

Total Weight (with packaging):

Approx. 1304g/ 2.87 lbs

Technical Data Cont.

Transmission Range :

Approx. 10m / 32.80'

Frequency Range:

2.400 GHz - 2.4835 GHz

Storage Temperature:

-20°C to 65°C / -4°F to 149°F

Operating Temperature:

0° C - 40° C / 32° F - 104° F

Current Consumption:

Typ. 3 mA (keyboard), Typ. 10 mA (mouse), Typ. 30 mA (receiver)

Interface:

USB

Connection Sockets:

- Low voltage socket for USB charging cable

Product Approvals:

UL 

c-tick 

CE 

FCC 

TÜV/GS 

System Requirements:

USB port for wireless receiver (second free USB port for using the charger cable during operation)

Delivery Volume:

- 1 signal receiver
- USB charger cable
- Operating instructions in hard copy
- 1 optical wireless mouse
- 1 wireless keyboard
- 2 LSD NiMH batteries (type AAA)
- 2 LSD NiMH batteries (type AA)



Technical Data Cont.

Dimensions (product):

460 x 165 x 15 mm / 18.11"x
6.49"x .59" (keyboard), 115 x 60 x
35mm / 4.52" x 2.36"x 1.37"
(mouse), 42 x 18 x 8 mm / 1.65"x
.70"x .31" (receiver)

Packaging Dimensions:

Approx. 570 x 170 x 45 mm /
22.4"x 6.6" x 1.7"

Mouse:

- Scanning: Infrared
- Resolution: 1000 / 2000 dpi (adjustable)
- Number of Keys: 3
- Mouse Wheel Design: Scroll Wheel with Key Function

- Design: Symmetrical
- Connection: Wireless
- Housing Color: Black
- Key Color: Black

Keyboard:

- Key technology: SX
- Service Life, Standard Key: > 10 Million Key Operations
- Inscription Layout: Standard
- Number of Keys: 104 + 4
- Number of Additional keys:4

Packaging Unit:

Number of Products in the Master Package: 6
Number of Master Packages per Pallet: 24

Warranty:

2 years

<i>Order Number</i>	<i>Color</i>	<i>Number of Keys</i>
JD-0400EU-2	Black	104+4 Keys

ZF Electronic Systems Pleasant Prairie, LLC
11200 88th Avenue
Pleasant Prairie, WI 53158
USA
Phone: 262.942.6500
Internet: www.cherrycorp.com

Sales: 262.942.6500
E-Mail: cep_sales@ZF.com
Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.