CHERRY KC 4500 ERGO



Image: JK-4500EU-2

Models may vary from the image shown

Relaxed and comfortable through the whole day's work.

Do you suffer from tense shoulders, cramp or other unpleasant symptoms when working on the computer? In many cases this is caused by incorrect posture.

Simple relief can be provided by an ergonomic keyboard such as the CHERRY KC 4500 ERGO. With its special design, your hands and arms take up a more natural position by themselves. This relieves your shoulders and back and your relaxed posture reduces stress. The extra-soft palm rest with memory foam prevents pressure points and lets you rest your hands comfortably.

The three feet allow you to raise the front of keyboard. This position is particularly comfortable when working in a standing position. The rubber feet also reliably prevent the keyboard from slipping – whether it's standing up or not.

An extra long cable with a USB plug allows you to connect the keyboard to the computer without any problems, even if the computer is under the desk, for example. The plug & play CHERRY KC 4500 ERGO is ready for use without any additional software. With its elegant colors and modern design, it looks great on any desk.

Once you've become used to the special design, typing is the same as on any other CHERRY keyboard: easy and uncomplicated.

Multimedia functions (volume up/down/off, next/previous track, start/pause) are integrated in the F-keys. You can easily call them up by pressing the FN key at the same time.

To make your daily work even easier, the free CHERRY KEYS software offers many customization options. CHERRY KEYS allows quick access to apps, files, individual text modules or macros at the touch of a key.

Function & performance

- → The design of the USB keyboard supports an ergonomic posture when using the computer
- → Curved keypad adapted to the movement of the hands and fingers for fatigue-free typing
- → Soft padded palm rest with memory foam and high-quality PU leather
- $\rightarrow\,$ Sturdy, fold-out feet on the underside for adjustable keyboard angle
- → 1.8 m long, flexible cable for easy setup
- → Additional commands such as volume up/down on the F buttons
- → Configurable keys with optional, free CHERRY KEYS software

CHERRY KC 4500 ERGO

Technical Data

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

approx. 750 g / 1.65 lb

Total weight (with packaging):

approx. 1126 g / 2.48 lb

Cable Length:

approx. 180 cm / 457.2 in

Storage Temperature:

-20°C to 60°C / -4° F to 140° F

Operating Temperature:

0°C to 40°C / 32° F to 104° F

Current Consumption:

typ. 10mA

Interface:

USB

Reliability:

MTBF (90) > 80000 hours

Product approvals:

CE

FCC

cTUVus

WHQL Win 10 64-bit

Dimensions (product):

approx. 475 x 258 x 42 mm / 18.70 x 8.53 x 1.39 in

(with feet up: 435mm / 1.67 in)

Packaging dimensions:

Single carton: approx. 476 x 258 x 45 mm /18.74 x 10.16 x 1.77 in Master carton: approx. 490 x 465 x 283 mm / 19.29 x 18.31 x 11.14 in

Keyboard:

- Service life, standard key: > 10 million key operations
- Number of Keys: Product dependant, see table "Models"
- Number of Hotkeys: 3 (PC look, Calculator, FN)
- Multimedia functions (Key F1 to F6 + FN): Volume down,
 Sound on/off, Volume up, Previous title, Next title, Play/pause
- Soft padded palm rest with memory foam and high-quality PU leather, not removable

System requirements:

USB connection

Windows 7, 8 or 10

Delivery Volume:

- CHERRY KC 4500 ERGO
- Operating instructions

Packaging Unit:

Number of products in the master package: 10 Number of master packages per pallet: 10

Warranty

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below.

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

CHERRY KC 4500 ERGO



Models:

Possible country/layout versions

	Product name	Order number	Layout (country or language)	Housing colour	Key colour	Number of keys	EAN Code
1	CHERRY KC 4500 ERGO	JK-4500BE-2	Belgium	Black	Black	109 +3	4025112094941
2	CHERRY KC 4500 ERGO	JK-4500CH-2	Switzerland	Black	Black	109 + 3	4025112093968
3	CHERRY KC 4500 ERGO	JK-4500DE-2	Germany	Black	Black	109 + 3	4025112093937
4	CHERRY KC 4500 ERGO	JK-4500EU-2	US English with EURO symbol	Black	Black	108 + 3	4025112093920
5	CHERRY KC 4500 ERGO	JK-4500FR-2	France	Black	Black	109 + 3	4025112093944
6	CHERRY KC 4500 ERGO	JK-4500GB-2	UK	Black	Black	109 + 3	4025112093951
7	CHERRY KC 4500 ERGO	JK-4500PN-2	Pan-Nordic	Black	Black	109 + 3	4025112093975
8	CHERRY KC 4500 ERGO	JK-4500ES-2	Spain	Black	Black	109 + 3	4025112096457