



F  
 D  
 C  
 B  
 A

DIMENSIONS IN INCHES (MILLIMETERS) Dwg. No.  
 DO NOT SCALE DRAWING ..... GRL-4011-1600



**RATINGS:**

UL CSA  
 16A AC 125-250 VAC 10A 14 VT  
 3/4 HP 125-250 VAC 3A 125 VL

HOUSING COLOR: BLACK  
 BUTTON COLOR: RED

1	2	3	4	5	6	7	8	9	10	
<b>REVISIONS</b> 0 RELEASED. SPR 2-11-91 RBK 2-13-91 1 UPDATED & REDRAWN. CORRECTED POSITION OF .320±.010 & RELOCATED .340±.010. DGW 6-12-95 JUN. 20, 1996 2 REDRAWN WITH NEW FORMAT. ADDED RATINGS, BUTTON & HOUSING COLORS. DGW 3-15-2010 <b>G.G. MAR 15 2010</b>							<b>CW INDUSTRIES</b> Southampton, Pa. 18966 TOLERANCES UNLESS OTHERWISE SPECIFIED 2 Place Decimal ±.010 METRIC 3 Place Decimal ±.005 1 Place Dec. ±.25mm Angles ..... ±1' 2 Place Dec. ±.13mm		Title: <b>ASSEMBLY DRAWING          ROCKER SWITCH          S.P.- S.T.</b>	
Made for: CW IND. Drawn by: DGW 3-15-2010 Checked by: <i>G. Gold 3-15-10</i> Approval: <i>G. Gold 3-15-10</i>							Division: <b>SWITCH</b>		Dwg. No. <b>GRL-4011-1600</b>	

MASTER