FIBOX
Enclosing innovations

ARCA AR865CHSSLT

Sample photo

Order symbol:	AR865CHSSLT	**EAN**:	6418074066701
Product nbr:	8561037	**El. number**:	
Description:	PC Enclosure	**Finland**:	
Remarks:	Hinged transparent cover w/S.S. Lockable latch		

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:	Length	Width	Height
mm:	203	152	127
inch:	8.0	6.0	5.0

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Stainless steel
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:	
Temperature °C (short term):	-40 … 140 °C
Temperature °C (continuous):	-40 … 80 °C
Temperature °F (short term):	-40 … 284 °F
Temperature °F (continuous):	-40 … 175 °F

Accessories:	
ABP86	Painted Steel Back Panel

Accessories:	
ALBP86	Aluminum Back Panel
ADFP86	Dead Front Panel w/ screws
ASP86	Aluminum Swing Panel
ASPK86	Swing Panel Kit incl. Panel
ASPHK8	Swing Panel Kit w/o Panel
AMFL6	6" Mounting Flange Set

Rating:

Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK07/IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 508
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13