# Twist-Lock<sup>®</sup> Devices 20A, 125V, 2 Pole, 3 Wire Grounding Spring Termination Single Flush Receptacle

#### **Features**

- · Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- · High-impact, abuse-resistant nylon face
- Face color coding by voltage facilitates locating and mating of proper devices

### **Ordering Information**

DescriptionDevice ColorUPCCatalog NumberNylon face, back wire.Black783585569543HBL2310ST

### Listings

Listed to UL 498 Certified to CSA C22.2 No.42

## **Specifications**

Face Nylon
Base Nylon
Contacts Brass
Spring Steel
Mounting Strap Brass

#### **Performance**

**Electrical** 

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation Solid/Stranded #14 AWG to #12 AWG

Terminal Identification Terminals identified in accordance with UL 498

**Environmental** 

Moisture Resistance

Flammability V2 or better per UL94/CSA 22.2 No.0.17

IP20 Suitability


Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o


impact)

# HUBBELL









# **Complementary Products**

Plug HBL2311
Wallplate or Weatherproof Cover 1.60" Opening
Switched Enclosure SETL3

#### Online Resources

Customer Use Drawing eCatalog Installation Instructions

