

Product Datasheet

[Catalog Home](#)
[Home Page](#)
[Search](#)


## SHC2037CR -- Cord Connectors



Black Nylon

Hubbell's nylon cord connectors resist most common industrial corrosive and provide effective pullout protection in a lightweight design. They are ideal for any application where weight, conductivity or corrosion may be an issue.

### Product Specifications

<b>Product Type</b>	Cord Connectors
<b>Material/Style</b>	Nylon Standard Style
<b>Cord Diameter Range</b>	.625" - .750" (15.8- 19.0)
<b>Cord Connector Body Style</b>	Straight Male
<b>Form Size</b>	F3
<b>HUB Size</b>	3/4"
<b>Color</b>	 Black
<b>Color Code</b>	Yellow
<b>Recommended Knockout Hole Size</b>	1.09" - 1.14" (27.8-29.0)
<b>Flammability</b>	Hubbell nylon cord connectors have a UL 94-V2 rating.
<b>Hazardous Locations</b>	Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b).
<b>Dimension A</b>	1.56" (39.6) Dia.
<b>Dimension B</b>	1.60" (40.6) Ref.
<b>Dimension C</b>	.55" (14.0)
<b>Dimension D</b>	.77" (19.6) Throat Dia.
<b>Dimension E A/C</b>	1.44" (36.6)
<b>Dimension E A/F</b>	1.31" (33.3)
<b>Certifications</b>	UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111.
<b>UPC Number</b>	78358545172
<b>Weight in LBs</b>	0.1
<b>Link to Drawing Library</b>	<a href="#">Click here for Library</a>
<b>Link to PDF Catalog</b>	<a href="#">Click here for Catalog</a>

