

Search



[All 3M Products](#) [Newsroom](#) [About 3M](#)

United States [Change](#)

Industrial Adhesives & Tapes

[Products](#) | [Applications](#) | [Industries](#) | [Capabilities](#) | [Support](#)

[Where to Buy](#)

[United States](#) > [All 3M Products](#) > [Manufacturing](#) > [Industrial Adhesives & Tapes](#) > [3M Tapes & 3M Adhesives](#) > [Fasteners](#) > [3M™ Hook and Loop](#) > [3M™ Fastener TB3526N/TB3527N Hook/Loop](#)

3M™ Fastener TB3526N/TB3527N Hook/Loop

UPC# 00051111976487 3M Product Number TB3526N/TB3527N

[Print](#)



★★★★★ [Write a review](#)


Our high performance PSA nylon hook and loop fasteners are coated on the backside with a high performance rubber based pressure sensitive adhesive. The adhesive is ideal for indoor use and bonds well to paper and cardboard, paint, bare and painted metal, glass, sealed wood, and many plastics, making these fasteners easily and conveniently attached to a variety of substrates.

Need Help?

[Share](#)

Questions? We can help
[Contact Us](#)

- Hook and loop fasteners create smooth joints without screws, rivets, bolts or zippers
- High performance rubber based adhesive sticks instantly to a variety of indoor substrates
- Woven nylon is durable for thousands of closures
- Fast, convenient means to create refastenable seams, joints and other closures



[Where to Buy](#)

Overview

Reviews

Our hook and loop product constitutes a 100 mil to 160 mil engaged thickness and uses a 3.0 mil white polypropylene film liner printed with our red 3M logo. Hook and loop fasteners are effective for securing fabric to furniture cushions, airplane seating, carpet panel attachments, uniforms, gloves and clothing. These types of applications are widely utilized in electronics, construction, specialty vehicle, military, medical, furniture, as well as general industrial operations where securing surfaces that can be unfastened and refastened thousands of times with no bulging rivets, screws or bolts is desired.

3M Fastener TB3526/TB3527 Trial Bags consist of nylon hooks and woven nylon loops which engage each other to form a quick fastening attachment and offer advanced closure alternatives to zippers, screws, snaps, hooks, etc. We designed 3M™ Hook and Loop Fasteners to improve appearance, function, and productivity versus these traditional reclosable fasteners. No drilling, no tightening. They offer greater design flexibility, faster product assembly, smoother and cleaner exterior surfaces and improved product performance in many applications.

3M Trial Bags Simplify Selection

3M™ Hook and Loop Fasteners Trial Bags provide a simplified "go-to" selection proven successful for most common applications, along with just the right length and quantity for trial run testing. With up to 5,000 closures for our standard products, 3M™ Hook and Loop Reclosable Fasteners offer a solution with a reliable pressure sensitive adhesive for a secure hold.

Attributes

Adhesive Type	High Performance Rubber Adhesive
Brand	3M
Closure Life	5000
Color	Black
Engaged Thickness	0.14 Inch
Flame Retardant	No
Hook/Loop	Hook/Loop
Industries	

Transportation, Specialty Vehicle, Construction, Furniture, Medical, Military & Government, General Industrial, Electronics

Length	10 Linear Foot
Length (Metric)	3.05 m
Liner Thickness	3 mil
Liner Type	White Polyethylene with Red Logo
Low Profile	No
Material	Nylon
Maximum Operating Temperature (Celsius)	49 Degree Celsius
Maximum Operating Temperature (Fahrenheit)	120 Degree Fahrenheit
Product Form	Bag
Width	1 Inch
Width (Metric)	25.4 mm

Reviews



[Be the first to review this product](#)

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2015. All Rights Reserved.