

Northern Technologies to AMP Cross Reference

NOTES: THE NAME AMP ALONG WITH THE AMP PART NUMBERS SHOWN ARE THE PROPERTY OF AMP INCORPORATED.
 COMPONENTS LISTED ARE CONSIDERED FUNCTIONAL EQUIVALENTS. MECHANICAL SPECIFICATIONS WILL VARY.
 PART NUMBERS LISTED ARE PACKAGED CARRYING THE NORTHERN TECHNOLOGIES LOGO.
 NO LOGO AND BULK PARTS ARE AVAILABLE - CONSULT FACTORY FOR FURTHER DETAILS.
 * WITH GROMMETS
 ** WITH FERRULES

AMP PART NO.	Northern Technologies PART NO.	DETAILS
1-66504-0	DCTSX1020AF	FEMALE CRIMP CONTACTS LOOSE PIECE - 1,000 PIECES PER BAG
1-66506-0	DCTPX1020AF	MALE CRIMP CONTACTS LOOSE PIECE - 1,000 PIECES PER BAG
1-748390-1	DR315ST2I	FEMALE 15 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
1-748390-2	DR315ST2S	FEMALE 15 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
205203-1	DC9S	FEMALE 9 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205203-3	DC9ST	FEMALE 9 CONTACTS - TIN SHELL - GROUNDING INDENTS
205204-1	DC9P	MALE 9 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205204-4	DC9PTE	MALE 9 CONTACTS - TIN SHELL - GROUNDING INDENTS
205205-1	DC15S	FEMALE 15 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205205-2	DC15ST	FEMALE 15 CONTACTS - TIN SHELL - GROUNDING INDENTS
205206-1	DC15P	MALE 15 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205206-3	DC15PTE	MALE 15 CONTACTS - TIN SHELL - GROUNDING INDENTS
205207-1	DC25S	FEMALE 25 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205208-1	DC25P	MALE 25 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205209-1	DC37S	FEMALE 37 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205209-2	DC37ST	FEMALE 37 CONTACTS - TIN SHELL - GROUNDING INDENTS
205210-1	DC37P	MALE 37 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205210-3	DC37PTE	MALE 37 CONTACTS - TIN SHELL - GROUNDING INDENTS
205211-1	DC50S	FEMALE 50 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205211-2	DC50ST	FEMALE 50 CONTACTS - TIN SHELL - GROUNDING INDENTS
205212-1	DC50P	MALE 50 CONTACTS - YELLOW CHROMATE SHELL - GROUNDING INDENTS
205212-3	DC50PTE	MALE 50 CONTACTS - TIN SHELL - GROUNDING INDENTS
207463-1	DC25ST	FEMALE 25 CONTACTS - TIN SHELL - GROUNDING INDENTS
207464-2	DC25PTE	MALE 25 CONTACTS - TIN SHELL - GROUNDING INDENTS
66504-3	DCTSL520A30	FEMALE CRIMP CONTACTS ON REEL - 5,000 PIECES PER REEL
66504-4	DCTSL520AF	FEMALE CRIMP CONTACTS ON REEL - 5,000 PIECES PER REEL
66504-9	DCTSX1020A30	FEMALE CRIMP CONTACTS LOOSE PIECE - 1,000 PIECES PER BAG
66506-3	DCTPL520A30	MALE CRIMP CONTACTS ON REEL - 5,000 PIECES PER REEL
66506-4	DCTPL520AF	MALE CRIMP CONTACTS ON REEL - 5,000 PIECES PER REEL
66506-9	DCTPX1020A30	MALE CRIMP CONTACTS LOOSE PIECE - 1,000 PIECES PER BAG
** 745171-2/1/5	C88000218	METAL 09 POSITION WITH GROMMETS
** 745172-3/2/1	C88000207	METAL 15 POSITION WITH GROMMETS
** 745173-5/4/3/2/1	C88000203	METAL 25 POSITION WITH GROMMETS

Northern Technologies to AMP Cross Reference

NOTES: THE NAME AMP ALONG WITH THE AMP PART NUMBERS SHOWN ARE THE PROPERTY OF AMP INCORPORATED.
 COMPONENTS LISTED ARE CONSIDERED FUNCTIONAL EQUIVALENTS. MECHANICAL SPECIFICATIONS WILL VARY.
 PART NUMBERS LISTED ARE PACKAGED CARRYING THE NORTHERN TECHNOLOGIES LOGO.
 NO LOGO AND BULK PARTS ARE AVAILABLE - CONSULT FACTORY FOR FURTHER DETAILS.
 * WITH GROMMETS
 ** WITH FERRULES

AMP PART NO.	Northern Technologies PART NO.	DETAILS
** 745174-5/4/3/2/1	C88000206	METAL 37 POSITION WITH GROMMETS
** 745175-6/5/4/3/2/1	C88000208	METAL 50 POSITION WITH GROMMETS
** 745833-9/7/5/3/1	C88321000	MAEALIZED PLASTIC 25 POSITION WITH GROMMETS
** 745854-5/3/1	C88301000	METALIZED PLASTIC 09 POSITION WITH GROMMETS
** 745918-4/3/2/1	C88611002	METAL ETHERNET 15 POSITION 90 DEGREE WITH GROMMETS
** 745919	C88611000	METAL ETHERNET 15 POSITION (SHORT) WITH GROMMETS
** 745919	C88611001	METAL ETHERNET 15 POSITION (LONG) WITH GROMMETS
** 747098-9/7/5/3/1	C88341000	METALIZED PLASTIC 50 POSITION WITH GROMMETS
** 747099-7/5/3/1	C88311000	METALIZED PLASTIC 15 POSITION WITH GROMMETS
** 747100-9/7/5/3/1	C88331000	METALIZED PLASTIC 37 POSITION WITH GROMMETS
747841-3	DR15PTE2I	MALE 15 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
747843-3	DR37PTE2I	MALE 37 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
747904-2	D9PTES	MALE 9 CONTACTS (STAMPED) - TIN SHELL - GROUNDING INDENTS
747904-4	D9PS	MALE 9 CONTACTS (STAMPED) - YELLOW CHROMATE SHELL - GROUNDING INDENTS
747905-2	D9STS	FEMALE 9 CONTACTS (STAMPED) - TIN SHELL - GROUNDING INDENTS
747905-4	D9SS	FEMALE 9 CONTACTS (STAMPED) - YELLOW CHROMATE SHELL - GROUNDING INDENTS
747908-2	D15PTES	MALE 15 CONTACTS (STAMPED) - TIN SHELL - GROUNDING INDENTS
747908-4	D15PS	MALE 15 CONTACTS (STAMPED) - YELLOW CHROMATE SHELL - GROUNDING INDENTS
747909-2	D15STS	FEMALE 15 CONTACTS (STAMPED) - TIN SHELL - GROUNDING INDENTS
747912-2	D25PTES	MALE 25 CONTACTS (STAMPED) - TIN SHELL - GROUNDING INDENTS
747912-4	D25PS	MALE 25 CONTACTS (STAMPED) - YELLOW CHROMATE SHELL - GROUNDING INDENTS
747913-2	D25STS	FEMALE 25 CONTACTS (STAMPED) - TIN SHELL - GROUNDING INDENTS
747913-4	D25SS	FEMALE 25 CONTACTS (STAMPED) - YELLOW CHROMATE SHELL - GROUNDING INDENTS
747916-2	D37PTES	MALE 37 CONTACTS (STAMPED) - TIN SHELL - GROUNDING INDENTS
747916-4	D37PS	MALE 37 CONTACTS (STAMPED) - YELLOW CHROMATE SHELL - GROUNDING INDENTS
747917-2	D37STS	FEMALE 37 CONTACTS (STAMPED) - TIN SHELL - GROUNDING INDENTS
748333-2	DCHPL522A30	MALE CRIMP CONTACTS ON REEL - 5,000 PIECES PER REEL
748364-1	DC315PTE	MALE 15 CONTACTS - TIN SHELL - GROUNDING INDENTS
748365-1	DC326PTE	MALE 26 CONTACTS - TIN SHELL - GROUNDING INDENTS
748366-1	DC344PTE	MALE 44 CONTACTS - TIN SHELL - GROUNDING INDENTS
748367-1	DC362PTE	MALE 62 CONTACTS - TIN SHELL - GROUNDING INDENTS
748368-1	DC378PTE	MALE 78 CONTACTS - TIN SHELL - GROUNDING INDENTS
748394-5	DR362ST2I	FEMALE 62 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748394-6	DR362ST2S	FEMALE 62 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS

Northern Technologies to AMP Cross Reference

NOTES: THE NAME AMP ALONG WITH THE AMP PART NUMBERS SHOWN ARE THE PROPERTY OF AMP INCORPORATED.
 COMPONENTS LISTED ARE CONSIDERED FUNCTIONAL EQUIVALENTS. MECHANICAL SPECIFICATIONS WILL VARY.
 PART NUMBERS LISTED ARE PACKAGED CARRYING THE NORTHERN TECHNOLOGIES LOGO.
 NO LOGO AND BULK PARTS ARE AVAILABLE - CONSULT FACTORY FOR FURTHER DETAILS.
 * WITH GROMMETS
 ** WITH FERRULES

AMP PART NO.	Northern Technologies PART NO.	DETAILS
748481-5	DR326ST2I	FEMALE 26 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748481-6	DR326ST2S	FEMALE 26 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
748482-5	DR344ST2I	FEMALE 44 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748482-6	DR344ST2S	FEMALE 44 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
748565-1	DC315ST	FEMALE 15 CONTACTS - TIN SHELL - GROUNDING INDENTS
748566-1	DC326ST	FEMALE 26 CONTACTS - TIN SHELL - GROUNDING INDENTS
748567-1	DC344ST	FEMALE 44 CONTACTS - TIN SHELL - GROUNDING INDENTS
748568-1	DC362ST	FEMALE 62 CONTACTS - TIN SHELL - GROUNDING INDENTS
748569-1	DC378ST	FEMALE 78 CONTACTS - TIN SHELL - GROUNDING INDENTS
748610-2	DCHSL522A30	FEMALE CRIMP CONTACTS ON REEL - 5,000 PIECES PER REEL
* 748676-1	C88000218	METAL 09 POSITION WITH GROMMETS
* 748676-2	C88000207	METAL 15 POSITION WITH GROMMETS
* 748676-3	C88000203	METAL 25 POSITION WITH GROMMETS
* 748676-4	C88000206	METAL 37 POSITION WITH GROMMETS
* 748676-5	C88000208	METAL 50 POSITION WITH GROMMETS
* 748677-1	C88301000	METALIZED PLASTIC 09 POSITION WITH GROMMETS
* 748677-2	C88311000	METALIZED PLASTIC 15 POSITION WITH GROMMETS
* 748677-3	C88321000	METALIZED PLASTIC 25 POSITION WITH GROMMETS
* 748677-4	C88331000	METALIZED PLASTIC 37 POSITION WITH GROMMETS
* 748677-5	C88341000	METALIZED PLASTIC 50 POSITION WITH GROMMETS
* 748678-1	C88301004	TWO PIECE PLASTIC 09 POSITION WITH GROMMETS
* 748678-2	C88311004	TWO PIECE PLASTIC 15 POSITION WITH GROMMETS
* 748678-3	C88321004	TWO PIECE PLASTIC 25 POSITION WITH GROMMETS
* 748678-4	C88331004	TWO PIECE PLASTIC 37 POSITION WITH GROMMETS
* 748678-5	C88341005	TWO PIECE PLASTIC 50 POSITION WITH GROMMETS
748891-2	DL19ST2I	FEMALE 9 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748892-2	DL115ST2I	FEMALE 15 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748893-2	DL125ST2I	FEMALE 25 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748894-2	DL137ST2I	FEMALE 37 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748895-2	DL19PTE2I	MALE 9 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748896-2	DL115PTE2I	MALE 15 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748897-2	DL125PTE2I	MALE 25 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748898-2	DL137PTE2I	MALE 37 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
748971-2	DL19ST2S	FEMALE 9 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS

Northern Technologies to AMP Cross Reference

NOTES: THE NAME AMP ALONG WITH THE AMP PART NUMBERS SHOWN ARE THE PROPERTY OF AMP INCORPORATED.
 COMPONENTS LISTED ARE CONSIDERED FUNCTIONAL EQUIVALENTS. MECHANICAL SPECIFICATIONS WILL VARY.
 PART NUMBERS LISTED ARE PACKAGED CARRYING THE NORTHERN TECHNOLOGIES LOGO.
 NO LOGO AND BULK PARTS ARE AVAILABLE - CONSULT FACTORY FOR FURTHER DETAILS.
 * WITH GROMMETS
 ** WITH FERRULES

AMP PART NO.	Northern Technologies PART NO.	DETAILS
748972-2	DL115ST2S	FEMALE 15 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
748973-2	DL125ST2S	FEMALE 25 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
748974-2	DL137ST2S	FEMALE 37 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
748975-2	DL19PTE2S	MALE 9 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
748976-2	DL115PTE2S	MALE 15 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
748977-2	DL125PTE2S	MALE 25 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
748978-2	DL137PTE2S	MALE 37 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
749080-1	N90111000	CM HD 50C w/THUMBSCREWS NICKEL PLATE
749608-1	N91101000	CM HD 26C w/LATCHES - NICKEL PLATE
749621-2	A29002610	HD 26C IDC PLUG CONNECTOR
749621-5	A29005010	HD 50C IDC PLUG CONNECTOR
749621-7	A29006810	HD 68C IDC PLUG CONNECTOR
750752-1	C90001000	CM HD 68C BOOT KIT w/THUMBSCREWS
788362-1	N90620000	CM VHDCI 68C .365" - .402", w/M2 T.Screws, Ni Plated, PKG.
788750-1	DR9ST2I	FEMALE 9 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
788751-1	DR25ST2S	FEMALE 25 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
788752-1	DR25ST2I	FEMALE 25 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
788753-1	DR9PTE2S	MALE 9 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
788754-1	DR9PTE2I	MALE 9 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
788755-1	DR25PTE2I	MALE 25 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
788756-1	DR9ST2S	FEMALE 9 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
788757-1	DR15ST2I	FEMALE 15 CONTACTS WITH LOCKING FORKS & 4-40 THREADED INSERTS
788781-1	DR15ST2S	FEMALE 15 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS
788782-1	DR25PTE2S	MALE 25 CONTACTS WITH LOCKING FORKS & 4-40 FEMALE SCREWLOCKS