

# USB AC Adapter



## Features

- Folding, 2-Prong Plug
- Perfect for use with cell phones, tablets, MP3 players, handheld game systems, digital cameras, GPS devices and more!

## Specifications

### AC Input

Voltage Range: 100 – 240 VAC

Input Frequency: 50/60 Hz

Inrush Current: 400mA Max

### DC Output

Voltage: 5V

Current: 1A

### Ordering Information



NTE Type No.	DC Output		Plug Type
	Amps	Wattage	
NEW 57-5D-1000-U	1A	5	USB Standard Type A Receptacle

# 4-Port USB AC Adapter



## Features

- Folding, 2-Prong Plug
- Built-In Smart Chip Testing Fuses and Over-Temperature, Over-Current, Overload, and Short-Circuit Protection
- Perfect for use with smart phones, tablets, MP3 players, handheld game systems, digital cameras, GPS devices and more!

## Specifications

### AC Input

Voltage Range: 100 – 240 VAC

Input Frequency: 50/60 Hz

Inrush Current: 800mA Max.

### DC Output

Voltage: 5V

Current: 4A (2.1A Max one port, 4A Max all ports total)

### Ordering Information



NTE Type No.	DC Output		Plug Type
	Amps	Wattage	
NEW 57-5D-4000-U	4A	20	4 USB Standard Type A Receptacles