

Crimp insert - CRIMPFOX-M RC 6/DIE



1212079

<https://www.phoenixcontact.com/us/products/1212079>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Die, for Crimpfox-M, for non-insulated cable lugs 0.5 - 6 mm², packed in a serial storage box

Commercial Data

Item number	1212079
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	B14
Product Key	BH313Y
Catalog Page	Page 436 (C-3-2019)
GTIN	4046356454490
Weight per Piece (including packing)	76.2 g
Weight per Piece (excluding packing)	67.99 g
Customs tariff number	82032000
Country of origin	SE

Crimp insert - CRIMPFOX-M RC 6/DIE



1212079

<https://www.phoenixcontact.com/us/products/1212079>

Technical Data

Product properties

Product type	Die
Compression	Indent crimp

Crimping position 1

Min. cross section	0.5 mm ²
Max. cross section	2.5 mm ²
AWG min	22
AWG max	14

Crimping position 2

Min. cross section	4 mm ²
Max. cross section	6 mm ²
AWG min	12
AWG max	10

Connection data

Conductor connection

Cross section range, metric	0.5 mm ² ... 6 mm ²
-----------------------------	---

Dimensions

Width	75 mm
Height	25.5 mm
Length	114 mm

Material specifications

Color	black
-------	-------

Crimp insert - CRIMPFOX-M RC 6/DIE



1212079

<https://www.phoenixcontact.com/us/products/1212079>

Approvals



EAC

Approval ID: RU x-DE.xx08.B.02974

Crimp insert - CRIMPFOX-M RC 6/DIE



1212079

<https://www.phoenixcontact.com/us/products/1212079>

Classifications

ECLASS

ECLASS-9.0	21019290
ECLASS-10.0.1	21019290
ECLASS-11.0	21049090

ETIM

ETIM 8.0	EC011823
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com