

# Spacer plate - DP-UK 3-MVSTB



3002445

<https://www.phoenixcontact.com/us/products/3002445>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Spacer plate, pitch: 0 mm, length: 47.7 mm, width: 2.4 mm, number of positions: 1, color: gray



## Commercial Data

Item number	3002445
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to Order (non-returnable)
Sales Key	B01
Product Key	BE1Z1X
Catalog Page	Page 323 (CL-2005)
GTIN	4017918090265
Weight per Piece (including packing)	2.067 g
Weight per Piece (excluding packing)	2.043 g
Customs tariff number	39269097
Country of origin	PL

# Spacer plate - DP-UK 3-MVSTB



3002445

<https://www.phoenixcontact.com/us/products/3002445>

## Technical Data

### Product properties

Product type	Partition plate
Number of positions	1
Pitch	0 mm

### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	gray
Material	PA

### Dimensions

Width	2.4 mm
Length	47.7 mm
Pitch	0 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# Spacer plate - DP-UK 3-MVSTB



3002445

<https://www.phoenixcontact.com/us/products/3002445>

## Classifications

### ECLASS

ECLASS-9.0	27141133
ECLASS-10.0.1	27141133
ECLASS-11.0	27141133

### ETIM

ETIM 8.0	EC000886
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# Spacer plate - DP-UK 3-MVSTB



3002445

<https://www.phoenixcontact.com/us/products/3002445>

## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)