



**SPECIFICATIONS:**

Type	Multi-Mode	Single Mode	LENGTH (L)	TOLERANCE
Insertion Loss	≤ 0.5dB	≤ 0.2dB	< 1M	+50mm/-0
Return Loss	≥ 20dB	≥ 55dB	≥ 1M < 10M	+100mm/-0
Test Wavelength	850nm	1310nm	≥ 10M < 30M	+150mm/-0
			≥ 30M	+1%/-0

**LENGTH TOLERANCE:**

	Designed By	JUNE.L	2009.09.16	DESC.	DX LC-LC JUMPER
	Checked By				
	Approved By			DRG. No.	H01-LCLC-002
Scale					
Version					

**QUEST**  
 TECHNOLOGY  
 INTERNATIONAL, Inc.  
 Quest Technology Int'l, Inc.  
 11200 NW 138th St., Meeley, FL 33178  
 Tel: 305-513-8893 Fax: 305-513-9875  
 www.QuestTechnologyInt.com