

Quick Reference

Search by part #

Check distributor part inventory

Products

Browse Products

-By Device - 6

-By Product Line- 6

-Attachment Methods 6

-Interface Materials - 6

-Accessories - 6

Useful Links

- [MSDS Safety Sheets](#)
- [How to Order?](#)
- [Find Sales Rep](#)
- [Find Distributor](#)
- [Sample Request](#)
- [Catalog Request](#)
- [Building a Part #](#)
- [Part # Cross Ref](#)

Accessories
Standard Mounting Pads

The following Mounting Pads are for use with TØ

<p>7717-167DAPG</p> <p>(DAP)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 8.71 (0.343)</p> <p>Thickness: 3.18 (0.125)</p> <p>RoHS Compliant</p>	
<p>7717-167NG</p> <p>(nylon)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 8.71 (0.343)</p> <p>Thickness: 3.18 (0.125)</p> <p>RoHS Compliant</p>	
<p>7717-161DAPG</p> <p>(DAP)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 8.64 (0.340)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p>	
<p>7717-161NG</p> <p>(nylon)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 8.64 (0.340)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p>	
<p>7717-159NG</p> <p>(nylon)</p> <p>Leads: 5</p> <p>Outside Diameter mm (in): 9.53 (0.375)</p> <p>Thickness: 5.59 (0.220)</p> <p>RoHS Compliant</p>	
<p>7717-158TG</p> <p>(Teflon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 9.91 (0.390)</p> <p>Thickness: 0.25 (0.010)</p> <p>RoHS Compliant</p>	
<p>7717-131DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 8.89 (0.350)</p> <p>Thickness: 0.97 (0.038)</p> <p>RoHS Compliant</p>	
<p>7717-131NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 8.89 (0.350)</p> <p>Thickness: 0.97 (0.038)</p> <p>RoHS Compliant</p>	
<p>7717-114NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 9.02 (0.355)</p> <p>Thickness: 1.17 (0.046)</p> <p>RoHS Compliant</p>	
<p>7717-4DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 9.53 (0.375)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-4NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 9.53 (0.375)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-5DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 8.89 (0.350)</p> <p>Thickness: 3.18 (0.125)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-5NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 8.89 (0.350)</p> <p>Thickness: 3.18 (0.125)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-15DAPG</p> <p>(DAP)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 8.89 (0.350)</p> <p>Thickness: 0.51 (0.020)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-15NG</p> <p>(nylon)</p> <p>Leads: 4</p> <p>Outside Diameter mm (in): 8.89 (0.350)</p> <p>Thickness: 0.51 (0.020)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-3DAPG</p> <p>(DAP)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 8.71 (0.343)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-3NG</p> <p>(nylon)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 8.71 (0.343)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-79DAPG</p> <p>(DAP)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 9.02 (0.355)</p> <p>Thickness: 0.97 (0.038)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-79NG</p> <p>(nylon)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 9.02 (0.355)</p> <p>Thickness: 0.97 (0.038)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-178DAPG</p> <p>(DAP)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 8.89 (0.350)</p> <p>Thickness: 0.53 (0.021)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-178NG</p> <p>(nylon)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 8.89 (0.350)</p> <p>Thickness: 0.53 (0.021)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-86DAPG</p> <p>(DAP)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 8.71 (0.343)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-86NG</p> <p>(nylon)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 8.71 (0.343)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p> <p>Product Change Notice</p>	
<p>7717-22NG</p> <p>(nylon)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 8.71 (0.343)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p>	
<p>7717-22DAPG</p> <p>(DAP)</p> <p>Leads: 3</p> <p>Outside Diameter mm (in): 8.71 (0.343)</p> <p>Thickness: 1.91 (0.075)</p> <p>RoHS Compliant</p>	
<p>7717-238NG</p> <p>(nylon)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 10.16 (0.400)</p> <p>Thickness: 4.06 (0.160)</p> <p>RoHS Compliant</p>	
<p>7717-300NG</p> <p>(nylon)</p> <p>Leads: Universal</p> <p>Outside Diameter mm (in): 11.18 (0.440)</p> <p>Thickness: 9.65 (0.380)</p> <p>RoHS Compliant</p>	
<p>7717-94NG</p> <p>(nylon)</p> <p>Leads: 4-Mar</p> <p>Outside Diameter mm (in): 8.89 (0.350)</p> <p>Thickness: 0.97 (0.038)</p> <p>RoHS Compliant</p>	