


» Max Clips
MAX10NG



Long standard force clip

Width:12.00
Force:40 N [9.0 lbs]
Thickness:0.60
RoHS:compliant
PCN Link:<https://www.aavid.com/sites/default/files/pcn/PCN121411.pdf>

ENTER QTY:

Need assistance?
 Call us: 1-855-32-AAVID
 Email: estore@aavid.com
 » [Help Page](#)

- > [Request a Sample](#)
- > [Request a Quote](#)
- > [Ask an Engineer](#)

The Fine Print
[Product Return Policy](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Customer Assistance

- [Contact Us](#)
- [Find a Distributor](#)
- [Find a Sales Rep](#)
- [Request a Quote](#)
- [Get Design Assistance](#)
- [Terms and Conditions](#)
- [Returns](#)

Popular Products

- [Fans Heat Sinks](#)
- [Extrusions](#)
- [Board Level](#)
- [Liquid Cooling](#)
- [Heat Pipe Technology](#)
- [Heat Sink Accessories](#)
- [Interface Materials](#)

Our Company

- [News and Events](#)
- [Management Team](#)
- [Worldwide Locations](#)
- [Disclaimer](#)
- [Customer Survey](#)
- [Privacy Policy](#)
- [Careers](#)

Connect with Aavid

Like / Follow / Connect
  

© Copyright 2017 Aavid Thermalloy, LLC.