

PRODUCT-DETAILS

ST201M-B20

Miniature Circuit Breaker - ST200M - B



General Information

Extended Product Type	ST201M-B20
Product ID	2CDS271334R0205
EAN	4016779017428
Catalog Description	Miniature Circuit Breaker - ST200M - B
Long Description	ST201M-B20 Miniature Circuit Breaker ST201M-B20 Miniature Circuit Breaker B-Char., 10kA, 20A, 1P

Technical

Standards	CSA 22.2 No. 235 IEC/EN 60947-2 UL 1077
Tripping Characteristic	B
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu})	(230 V AC) 15 kA
Rated Service Short-Circuit Breaking Capacity (I_{cs})	(230 V AC) 11.2 kA
Terminal Type	Double Clamp

Environmental

RoHS Status	Following EU Directive 2011/65/EU
-------------	-----------------------------------

Technical UL/CSA

Interrupting Rating acc. to UL1077	(277 V AC) 10 kA (60 V DC) 10 kA
---------------------------------------	-------------------------------------

Dimensions

Product Net Width	17.5 mm
Product Net Depth / Length	69 mm
Product Net Height	88 mm
Product Net Weight	0.115 kg

Container Information

Package Level 1 Units	carton 1 piece
Package Level 1 Width	24 mm
Package Level 1 Depth / Length	92 mm
Package Level 1 Height	80 mm
Package Level 1 Gross Weight	0.13 kg
Package Level 1 EAN	4016779030748

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85362010

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CDK400679D2703
Instructions and Manuals	9AKK107046A3150
RoHS Information	2CDK400679D2703

Popular Downloads

Data Sheet, Technical Information	9AKK107046A3150
Instructions and Manuals	9AKK107046A3150

Classifications

ETIM 6	EC000042 - Miniature circuit breaker (MCB)
ETIM 7	EC000042 - Miniature circuit breaker (MCB)
ETIM 8	EC000042 - Miniature circuit breaker (MCB)
eClass	V11.0 : 27141901
UNSPSC	39121614

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs

