

RB121-24VUC



RB121-24VUC Interface relay R600 1c/o,A1-A2=24VAC/DC,5-250VAC/60mA-6A

General Information

Extended Product Type	RB121-24VUC
Product ID	1SNA645001R0300
EAN	4013614507717
Catalog Description	RB121-24VUC Interface relay R600 1c/o,A1-A2=24VAC/DC,5-250VAC/60mA-6A
Long Description	Screw relay RB121-24VUC: 24VAC/DC Rated control supply voltage/ 1 SPDT output contact rated 5-250VAC, 60mA up to 6A with integrated LED

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85364900

Popular Downloads

Data Sheet, Technical Information	1SVC117001D0200
Instructions and Manuals	1SVC645000M9000

Dimensions

Product Net Width	6 mm
Product Net Height	67.5 mm
Product Net Depth / Length	70 mm
Product Net Weight	0.02 kg

Technical

Function	Boxed interface relay R600
Sub-Function	Relay with built in LED
Output	1 c/o (SPDT) contact
Output Signal	5 ... 250VAC / 60mA ... 6A
Rated Control Supply Voltage (U _s)	24 V AC/DC
Terminal Type	Screw Terminals

Environmental

RoHS Status

Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

CB Certificate	CB_DK-53188-UL
CCC Certificate	CCC_2017010303941444
CSA Certificate	CSA_254821
cUR Certificate	cUR_E352056
Declaration of Conformity - CE	1SVD982016-0001
EAC Certificate	EAC_RU_C-FR.ME77.B.01634
Instructions and Manuals	1SVC645000M9000
LR Certificate	LR_16_20068
RoHS Information	1SVD982016-0001
UR Certificate	UR_E352056

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	73 mm
Package Level 1 Height	71 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Gross Weight	0.25 kg
Package Level 1 EAN	3472596450014

Classifications

Object Classification Code	K
ETIM 4	EC001437 - Switching relay
ETIM 5	EC001437 - Switching relay
ETIM 6	EC001437 - Switching relay
ETIM 7	EC001437 - Switching relay
eClass	7.0 27371601
E-Number (Sweden)	4001127

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

