

RB122G-24VUC



RB122G-24VUC Interface relay R600 2c/o,A1-A2=24VAC/DC,5-250VAC/10mA-8A

General Information

Extended Product Type	RB122G-24VUC
Product ID	1SNA645012R2500
EAN	4013614507816
Catalog Description	RB122G-24VUC Interface relay R600 2c/o,A1-A2=24VAC/DC,5-250VAC/10mA-8A
Long Description	Screw relay RB122G-24VUC: 24VAC/DC Rated control supply voltage/ 1 DPDT gold plated output contact rated 5-250VAC, 10mA up to 8A with integrated LED

Ordering

Minimum Order Quantity	5 piece
Customs Tariff Number	85364900

Popular Downloads

Data Sheet, Technical Information	1SVC117001D0200
Instructions and Manuals	1SVC645000M9000

Dimensions

Product Net Width	12 mm
Product Net Height	67.5 mm
Product Net Depth / Length	70 mm
Product Net Weight	0.04 kg

Technical

Function	Boxed interface relay R600
Sub-Function	Relay with built in LED
Output	2 c/o (SPDT) contacts
Output Signal	5 ... 250VAC / 10mA ... 8A
Rated Control Supply Voltage (U_s)	24 V AC/DC
Terminal Type	Screw Terminals

Environmental

RoHS Status

Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

CB Certificate	CB_DK-53188-UL
CCC Certificate	CCC_2017010303941444
CSA Certificate	CSA_254821
cUR Certificate	cUR_E352056
Declaration of Conformity - CE	1SVD982016-0001
EAC Certificate	EAC_RU_C-FR.ME77.B.01634
Instructions and Manuals	1SVC645000M9000
LR Certificate	LR_16_20068
RoHS Information	1SVD982016-0001
UR Certificate	UR_E352056

Container Information

Package Level 1 Units	5 piece
Package Level 1 Width	73 mm
Package Level 1 Height	71 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Gross Weight	0.24 kg
Package Level 1 EAN	3472596450120

Classifications

Object Classification Code	K
ETIM 4	EC001437 - Switching relay
ETIM 5	EC001437 - Switching relay
ETIM 6	EC001437 - Switching relay
ETIM 7	EC001437 - Switching relay
eClass	7.0 27371601
E-Number (Sweden)	4001146

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Interface Relays and Optocouplers

