

Product Guide » ABB1SNA645021R2600

## OBIC0100-24VDC

[Print View..](#)  
[Print to Pdf..](#)

Products & Services only

+ Rate this page

+ Share this page

### Your preferences:

### ABB contact for Egypt

### General Information

Extended Product Type:	OBIC0100-24VDC
Product ID:	1SNA645021R2600
EAN:	3472596450212
Catalog Description:	OBIC0100-24VDC Optocoupler R600
Long Description:	Screw optocoupler OBIC0100 24vdc : 24vdc input / 5 upto 58vdc output 100mA



### Categories

Products » Low Voltage Products and Systems » Control Products »  
Electronic Relays and Controls » Interface Relays and Optocouplers

### Ordering

EAN:	3472596450212
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85364110

### Dimensions

Product Net Width:	6.0 mm
Product Net Height:	67.5 mm
Product Net Depth:	70.0 mm
Product Net Weight:	0.020 kg

### Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	73.0 mm
Package Level 1 Height:	71.0 mm
Package Level 1 Length:	80.0 mm
Package Level 1 Gross Weight:	0.230 kg

### Technical

Function:	Boxed optocoupler R600
Output:	solid-state output
Output Signal:	4.5 ... 58 V DC / 1 ... 100 mA
Rated Control Supply Voltage (U <sub>s</sub> ):	24 V DC
Terminal Type:	Screw Terminals

### Certificates and Declarations (Document Number)

CSA Certificate:	CSA_254821
cUR Certificate:	cUR_E352056
Declaration of Conformity - CE:	1SND225045C1000
EAC Certificate:	EAC_RU_C-FR.ME77.B.01634
LR Certificate:	LRS_0620042
UR Certificate:	UR_E352056

### Classifications

Object Classification Code:	K
ETIM 4.0:	EC001504 - Optocoupler
ETIM 5.0:	EC001504 - Optocoupler
UNSPSC:	43172000