




TE Connectivity: Every Connection Counts
 © 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

+ RELAYS, CONTACTORS & SWITCHES



TIME DELAY RELAYS



✓ Active

TE CONNECTIVITY (TE) SCERX22AEA=RLY,TRU OFF,120VAC/

1472958-1
 TE Internal Number: 1472958-1
 Alias ID: SCERX22AEA

[Not EU RoHS or ELV Compliant](#)
[Find Compliant Alternatives](#)

Type of Control **Knob**
 Input Voltage **120 VAC [125 VDC]**
 Contact Current Rating (A) **5A@120VAC, 5A@28VDC**
 Mode of Operation **Off-Delay**
 Delay Time **4 – 120 seconds**

Catalog Pages/Data Sheets

[5-1773450-5_sec12_SCE](#)
 PDF
 English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Relay Type	Time Delay
Product Category	Electromechanical Relays
Product Type	Relay

Configuration Features

Multiple Timing Ranges	With
------------------------	-------------

Electrical Characteristics

Input Voltage	120 VAC [125 VDC]
Actuating System	AC, DC

Contact Features

Type of Control	Knob
Contact Current Rating (A)	5A@120VAC, 5A@28VDC
Delay Time	4 – 120 seconds

	Contact Arrangement	2 Form C, DPDT, 2 C/O
Termination Features	Termination Type	8 or 11-Pin Octal Type Plug
Mechanical Attachment	Mounting Type	Socket
Dimensions	Dimensions (L x W x H) (Approximate)	100.33 x 50.038 x 50.038 mm [3.95 X 1.97 x 1.97in]
Usage Conditions	Operating Temperature Range (°C)	-30 – 65
Operation/Application	Mode of Operation	Off-Delay
Other	Repeatability (Max)	±1%
	Option	Knob Adjust
Product Compliance	Statement of Compliance PDF VIEW ALL PRODUCT COMPLIANCE	