

Product Details for GPD

No Image Available

GPD

Tyco Part Number:
1423155-5

 [Active](#)

Control Relays

[Not ELV or RoHS Compliant](#)

Product Highlights:

- ? GP Series
- ? Power
- ? DC Actuating System
- ? Input Voltage = 125 VDC
- ? Contact Arrangement = 1 Form C, SPDT, 1 C/O

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us](#)
- [About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Power
- ? Termination Type = 16 Flat Base Pins

Electrical Characteristics:

- ? Actuating System = DC
- ? Input Voltage (VDC) = 125
- ? Contact Rating = 10A Resistive @ 220 VAC/48 VDC

Body Related Features:

- ? [Series](#) = GP

Contact Related Features:

- ? Approved Standards = CSA Certified, UL Listed
- ? Approx. Dimensions (L x W x H) (mm [in]) = 45.00 x 45.00 x 109.00 [1.773 x 1.773 x 4.294]
- ? Mounting Options = Socket

Configuration Related Features:

- ? [Contact Arrangement](#) = 1 Form C, SPDT, 1 C/O

Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- ? Temperature Range (°C) = 0 – 60

Other:

- ? Brand = Agastat