

## Product Details for GPDQ

No Image Available

### GPDQ

Tyco Part Number: 1-1423155-0

 [Active](#)

## Control Relays

[Not ELV or RoHS Compliant](#)

### Product Highlights:

- ? GP Series
- ? Power
- ? DC Actuating System
- ? Input Voltage = 125 VDC
- ? Contact Arrangement = 1 Form C, SPDT, 1 C/O

[View all Features](#)

## Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us](#)
- [About This Product](#)

## Documentation & Additional Information

### Product Drawings:

- ? None Available

### Catalog Pages/Data Sheets:

- ? None Available

### Product Specifications:

- ? None Available

### Application Specifications:

- ? None Available

### Instruction Sheets:

- ? None Available

### CAD Files:

- ? None Available

### Additional Information:

- ? [Product Line Information](#)

### Related Products:

- ? [Tooling](#)

## Product Features

(Please use the Product Drawing for all design activity)

### Product Type Features:

- ? Product Type = Power
- ? Termination Type = 16 Flat Base Pins

### Electrical Characteristics:

- ? Actuating System = DC
- ? Input Voltage (VDC) = 125
- ? Contact Rating = 10A Resistive @ 220 VAC/48 VDC

### Body Related Features:

- ? [Series](#) = GP

### Contact Related Features:

- ? Approved Standards = CSA Certified, UL Listed
- ? Option = Coil Energization Light
- ? Approx. Dimensions (L x W x H) (mm [in]) = 45.00 x 45.00 x 109.00 [1.773 x 1.773 x 4.294]
- ? Mounting Options = Socket

### Configuration Related Features:

- ? [Contact Arrangement](#) = 1 Form C, SPDT, 1 C/O

### Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process

### Conditions for Usage:

- ? Temperature Range ( °C) = 0 – 60

### Other:

- ? Brand = Agastat