



GPI Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

Control Relays

GPI=RLY,120VAC

GPI

TE Internal Number: 1423156-1

Product Highlights [View All](#)

- Relay Style = Power
- GP Series
- AC Actuating System
- Input Voltage = 120 VAC
- Contact - Arrangement = 4 Form C (4PDT)

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#)

[Features](#)

[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Mechanical Attachment

Mounting Options Socket

Electrical Characteristics

Actuating System AC

Input Voltage (VAC) 120

Contact Rating 10A Resistive @ 220 VAC/48 VDC

Termination Features

Termination Type 16 Flat Base Pins

Dimensions

Approx. Dimensions (L x W x H) (mm [in]) 45.00 x 45.00 x 109.00 [1.773 x 1.773 x 4.294]

Configuration Features

Relay Style Power

Contact - Arrangement ? 4 Form C (4PDT)

Industry Standards

Approved Standards CSA Certified, UL Listed

RoHS/ELV Compliance ? Not ELV/RoHS compliant

Lead Free Solder Processes ? Not relevant for lead free process

Conditions for Usage

Temperature Range (°C) 0 - 60

Other

Series ? GP

Brand Agastat

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

