

## product details

### Product Searches

- [7/16](#)
- [1.0/2.3](#)
- [1.6/5.6](#)
- [AFI](#)
- [AMC](#)
- [BNC / RP-BNC](#)
- [C](#)
- [FAKRA SMB](#)
- [FME](#)
- [HN](#)
- [MCX](#)
- [Mini-UHF](#)
- [Mini 75 ? SMB](#)
- [MMCX](#)
- [Precision \(APC\)](#)
- [QMA](#)
- [SC](#)
- [SlimLine BNC](#)
- [SMA / RP-SMA](#)
- [SMB](#)
- [SMC](#)
- [SMP](#)
- [SSMB](#)
- [TNC / RP-TNC](#)
- [Triax](#)
- [True 75 ? BNC](#)
- [Tw in BNC](#)
- [Tw inax](#)
- [Type F](#)
- [Type G](#)
- [Type N](#)
- [UHF](#)
- [Reverse Polarity](#)



*Please note: Images are for reference only*

<b>Amphenol Part Number:</b>	031-15
<b>Product Series:</b>	<a href="#">BNC</a>
<b>Product Type:</b>	<a href="#">Connectors</a> » <a href="#">Cable</a>
<b>Application:</b>	<a href="#">Clamp</a>
<b>Body Plating:</b>	<a href="#">Nickel</a>
<b>Body Termination:</b>	<a href="#">Clamp</a>
<b>Cable Group:</b>	<a href="#">E</a>
<b>Cable Type:</b>	<a href="#">Belden 8241</a> , <a href="#">Belden 8279</a> , <a href="#">RG-140</a> , <a href="#">RG-59</a>
<b>Connector Body Style:</b>	<a href="#">Straight</a>
<b>Contact Plating:</b>	<a href="#">Silver</a>
<b>Contact Termination:</b>	<a href="#">Solder</a>
<b>Gender:</b>	<a href="#">Jack</a>
<b>Grade:</b>	<a href="#">Industrial</a>
<b>Impedance:</b>	<a href="#">50 Ohm</a>
<b>RoHS Certificate:</b>	<a href="#">Yes</a>
<b>More Information:</b>	<a href="#">Assembly Instructions</a> <a href="#">Customer Drawing</a> <a href="#">Distributor Inventory</a>

- [Adapters](#)
- [Cable Assemblies](#)
- [Tools](#)
- [Accessories](#)

[Product Search](#)

[Inventory Search](#)