

- [Amphenol Worldwide](#)
- [Amphenol RF Employment](#)
- [Engineering Focus](#)
- [Quality Focus](#)
- [Weather and Directions](#)
- [Locate A Distributor](#)
- [Check Distributor Inventory](#)
- [Frequency Range Chart](#)
- [Glossary](#)
- [Technical Questions](#)
- [VSWR Calculator](#)
- [VSWR Chart](#)
- [Customer Drawings](#)
- [Assembly Instructions](#)
- [Catalog](#)
- [Product Overview](#)
- [Product Search](#)
- [Cross Reference](#)
- [QPL Products](#)
- [Markets Served](#)
- [Product Literature](#)
- [Newsletter](#)
- [Customer Extranet](#)
- [Salesperson Extranet](#)
- [Vendor Extranet](#)
- [Employee Extranet](#)
- [Internal Employee Extranet](#)
- [Amphenol RF Manufacturers Rep.](#)

### Product Search

- [1.0/2.3](#)
- [1.6/5.6](#)
- [AFI](#)
- [AMC](#)
- [BNC / RPBNC](#)
- [C](#)
- [FAKRA SMB](#)
- [FME](#)
- [HD BNC](#)
- [HN](#)
- [MCX](#)
- [Mini BNC](#)
- [Mini UHF](#)
- [Mini 75 ? SMB](#)
- [MMCX](#)
- [Precision \(APC\)](#)
- [QMA](#)
- [SC](#)
- [SMA / RP-SMA](#)
- [SMB](#)
- [SMC](#)
- [SMP](#)
- [SSMB](#)
- [TNC / RP-TNC](#)
- [Triax](#)
- [True 75 ? BNC](#)
- [Twin BNC](#)
- [Twinax](#)
- [Type F](#)
- [Type G](#)
- [Type N](#)
- [UHF](#)
- [Reverse Polarity](#)

- [Adapters](#)
- [Tools](#)
- [Accessories](#)

[Product Search](#)  
src="/images/dottedline.gif"

>

[Inventory Search](#)

## product details



*Please note: Images are for reference only*

<b>Amphenol Part Number:</b>	000-6775-75
<b>Description:</b>	BNC 75ohm RG11 Plug
<b>Product Series:</b>	<a href="#">BNC</a>
<b>Product Type:</b>	<a href="#">Connectors</a> » <a href="#">Cable</a>
<b>Connector Body Style:</b>	<a href="#">Straight</a>
<b>Gender:</b>	<a href="#">Plug</a>
<b>Impedance:</b>	<a href="#">75 Ohm</a>
<b>RoHS Certificate:</b>	<a href="#">Yes</a>
<b>IGS File Download:</b>	<a href="#">IGS File</a>
<b>More Information:</b>	<a href="#">Assembly Instructions</a>
	<a href="#">Customer Drawing</a>
	<a href="#">Distributor Inventory</a>