

## product details

### Product Searches

[7/16](#)  
[1.0/2.3](#)  
[1.6/5.6](#)  
[AFI](#)  
[AMC](#)  
[BNC / RPBNC](#)  
[C](#)  
[FAKRA SMB](#)  
[FME](#)  
[HN](#)  
[MCX](#)  
[Mini BNC](#)  
[Mini-UHF](#)  
[Mini 75 Ohm SMB](#)  
[MMCX](#)  
[Precision \(APC\)](#)  
[QMA](#)  
[QWS](#)  
[SC](#)  
[SMA / RPSMA](#)  
[SMB](#)  
[SMC](#)  
[SMP](#)  
[SSMB](#)  
[TNC / RPTNC](#)  
[Triax](#)  
[Twin BNC](#)  
[Twinax](#)  
[Type F](#)  
[Type G](#)  
[Type N](#)  
[UHF](#)

[Adapters](#)  
[Cable Assemblies](#)  
[Tools](#)  
[Accessories](#)

[Product Search](#)

[Inventory Search](#)

image  
not yet  
available

*Please note: Images are for reference only*

**Amphenol Part Number:** 901-148-15  
**Product Series:** [SMA](#)  
**Product Type:** [Connectors](#) » [Cable](#)  
**Application:** [Solder](#)  
**Body Plating:** [Gold](#)  
**Body Termination:** [Solder](#)  
**Cable Group:** [C1](#)  
**Cable Type:** [RG-142, RG-400](#)  
**Connector Body Style:** [Right Angle](#)  
**Connector Material:** [Stainless Steel](#)  
**Contact Plating:** [Gold](#)  
**Contact Termination:** [Crimp](#)  
**Gender:** [Plug](#)  
**Impedance:** [50 Ohm](#)  
**RoHS Compliant:** [Yes](#)