

product details

Product Search

- [1.0/2.3](#)
- [1.6/5.6](#)
- [AFI](#)
- [AMC](#)
- [BNC / RP-BNC](#)
- [C](#)
- [FAKRA SMB](#)
- [FME](#)
- [HD BNC](#)
- [HN](#)
- [MCX](#)
- [Mini BNC](#)
- [Mini UHF](#)
- [Mini 75 Ω SMB](#)
- [MMCX](#)
- [Precision \(APC\)](#)
- [QMA](#)
- [SC](#)
- [SMA / RP-SMA](#)
- [SMB](#)
- [SMC](#)
- [SMP](#)
- [SSMB](#)
- [TNC / RP-TNC](#)
- [Triax](#)
- [True 75 Ω BNC](#)
- [Twin BNC](#)
- [Twinax](#)
- [Type F](#)
- [Type G](#)
- [Type N](#)
- [UHF](#)
- [Reverse Polarity](#)

- [Adapters](#)
 - [Tools](#)
 - [Accessories](#)
-
- [Product Search](#)
 - [Inventory Search](#)

image not yet available

[back](#)

Please note: Images are for reference only

Amphenol Part Number: [031-80901](#)

Product Series: [True 75Ohm BNC](#)

Product Type: [Connectors » Cable](#)

Body Plating: [Nickel](#)

Cable Group: [B1](#)

Cable Type: [Belden 9221, RG-179B, RG-187A M17/94-RG179](#)

Connector Body Style: [Right Angle](#)

Contact Plating: [Gold](#)

Gender: [Plug](#)

Grade: [Performance](#)

Impedance: [75 Ohm](#)

RoHS Certificate: [Yes](#)

IGS File Download: [IGS File](#)

More Information: [Customer Drawing](#)
[Distributor Inventory](#)