



Linegard | PGFR Series

15 / 20 Amp Linegard™ Series GFCI Duplex Receptacle

INTRODUCTION

The LineGard™ 15 / 20 Amp GFCI Duplex Receptacle is a ground fault circuit interrupter receptacle designed and manufactured by North Shore Safety, Ltd., a leader in innovated safety products. The PGFR series product come standard with power indicator light and series wire-through connections. Available in standard white and black, and come with decorative, impact-resistant nylon face plates. 2-year manufacturer's warranty.

SPECIFICATIONS	
Listing Type	UL Recognized, Class A UL 943, CSA 22.2 No. 144
Rated Supply Voltage	120 VAC
Rated Current	Up to 20 Amps or rating of wiring device and/or cable
Trip Level	5mA +/- 1mA (UL 943)
Operating Frequency	60 Hz
Response Time	25mS max
Operating Temperature	-35°C to 66°C
Operating Voltage Range	85% to 110% of rated VAC

DECISION TABLES

<u>Order Number</u>	<u>Voltage</u>	<u>Enclosure</u>
PGFR-120	120 VAC	15 / 20 White
PGFR-120	120 VAC	15 / 20 Black