

1-1734775-1 Product Details

[Share](#) | [Print](#) | [Email](#)


1-1734775-1

Universal Serial Bus (USB) Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- USB 2.0 Industry Standard
- Size = Standard
- A Series
- Receptacle
- Without Locking Feature

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 1-1734775-1

Active

[View 3D PDF](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

| Documentation & Additional Information | |
|---|---|
| <p>Product Drawings:</p> <ul style="list-style-type: none"> • USB CONNECTOR, RECEPTACLE, FLAG, R/A, DIP, A TYPE (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> • 2D Drawing (DXF, Version B) • 3D Model (IGES, Version B) • 3D Model (STEP, Version B) | <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling |

[List all Documents](#)

| Product Features (Please use the Product Drawing for all design activity) | |
|---|---|
| <p>Product Type Features:</p> <ul style="list-style-type: none"> • Size = Standard • Series = A • Gender = Receptacle • Number of Ports = 1 • Orientation = Flag • LED = Without <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Mount Location = Top <p>Termination Features:</p> <ul style="list-style-type: none"> • Contact Termination Type = Through Hole • Termination Method = Solder • Tail Length (mm [in]) = 3.3 [0.13] <p>Body Features:</p> <ul style="list-style-type: none"> • Locking Feature = Without • Panel Ground = Without • PCB Mount Retention Type = Kinked Leg(s) • Shell Plating = Nickel over Copper • Assembly Process Feature = Without Pick and Place Cover • Locating Post(s) = Without • Number of Positions = 4 | <p>Contact Features:</p> <ul style="list-style-type: none"> • Contact Plating, Mating Area, Material = Gold Flash over Palladium Nickel <p>Housing Features:</p> <ul style="list-style-type: none"> • Housing Color = Black <p>Industry Standards:</p> <ul style="list-style-type: none"> • Industry Standard = USB 2.0 • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant • USB-IF Test ID Number (TID) = Not Submitted For Testing <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Applies To = Printed Circuit Board • PCB Thickness, Recommended (mm [in]) = 1.60 [0.063] <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Tray <p>Other:</p> <ul style="list-style-type: none"> • Brand = Tyco Electronics |