



[CONNECTORS](#)

[FFC CONNECTORS](#)



✓ Active

TE CONNECTIVITY (TE)

010 HOUSING FFC RCPT 050CL SR

[FFC](#) | [FFC](#)

487973-1

TE Internal Number: 487973-1

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Connector Type Housing

Connector Style Receptacle

Connector System Wire-to-Board

Number of Positions 10

Centerline (Pitch) 1.27 mm [.05 in]

[↓ PRODUCT DRAWING](#)
English

DOCUMENTATION

Product Drawings

[HOUSING, RECEPTACLE, LATCH OFFSET, .050 C/L , FFC](#)

PDF

English

Product Specifications

Application Specification

[Flexible Flat Cable \(FFC\) Connectors For 1.27 Mm \(.050 In.\) Centerline Cable](#)

PDF

English

Product Specification

[.050 Inch Centerline FFC Cable Connector](#)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Type Housing

Connector Style Receptacle

Connector System Wire-to-Board

Connector & Contact Terminates To Wire & Cable

Type of Connector Slimline

Wire/Cable Type FFC

Product Type Connector

Configuration Features

Number of Positions 10

Number of Rows 1

Electrical Characteristics

Dielectric Withstanding Voltage (VAC) 300

Insulation Resistance (MΩ) 5000

Voltage 100 VAC

Body Features

Color Black

Contact Features

Contact Type Socket

Mechanical Attachment

Mating Connector Lock Type Latch

Mating Connector Lock With

Mating Alignment With

Panel Mount Retention Without

Mating Retention With

Mating Alignment Type Polarization

Housing Features

Centerline (Pitch) 1.27 mm [.05 in]

Housing Color Black

Housing Material Polyester

Usage Conditions

Operating Temperature Range (°C) -55 – 105

Flame Retardant Yes

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Method Bag

Packaging Quantity 1000

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
