Pistol Grip

Specially Developed to cover a wide range of IDC products - these tools are ideal for small batch production and repair

Image representative of type only

Features:

Interchangeable Heads
Complete cycle ratchect control
Product automatically indexes after insertion
Head rotates for user convenience



Part Number	Description	mm² (AWG) or other
548053-1	AMP CT 2.0 Receptacle Asssemblies	2 to 28 ways
870086-2	AMPMODU MT Female Connector, Dual Row	0.15 - 0.4 (26-22)
870086-3	AMPMODU MT Female Polarised Connectors, Dual Row	0.15 - 0.4 (26-22)
870088-3	HDE 20	0.05 - 0.6 (30-20)
946807-1	HE-13/14 (180°)	0.08 - 0.22 (28-24)
945419-1	HE-13/14 (90°)	0.08 - 0.22 (28-24)
539638-1	Modu w. pin housing 964144	1x5 way
549012-1	Modu w. pin housing 964144	1x4 way
734173-1	MT 6	0.4 - 1.0 (22-18)
656154-1	MT Connector - Decrete wire	2 to 20 Posns
734175-1	MT-6-M / Sonderversion	2 to 12 Posns
656154-5	MT-EDGE 5.0	0.5 (21)
873710-1	TANDEM-SPRING	2x13 way
549013-1	TS Receptacle	1x4 way

All options not always listed, please use our online search by terminal PN (where appropriate) to minimise cross-referencing errors, and contact us where information is unclear or missing as there may well be something available for your application.

Pistol Grip II

58074-1 - Manual Handle without Head 58075-1 - Pnuematic Handle without Head Ideal for small batch production and repair

Image representative of type only

Features:

Interchangeable Heads
Complete cycle ratchect control
Product automatically indexes after insertion
Head rotates for user convenience



Part Number	Description	mm² (AWG) or other
608868-1	Complete Tool, for AMPLIMITE HDE - 20	0.05 - 0.6 (30-20)
58579-1	Complete Tool, for MTA 100	0.08 - 0.4 (28-22)
58580-1	Complete Tool, for MTA 156	0.15 - 1.0 (26-18)
58336-1	Head only for AMPMODU MTE Receptacle	0.03 - 0.4 (30-22)
58569-1	Head only for AMPMODU MTE Receptacle	Inserts crimped Contacts into Housing
58246-2	Head only for MTA 100	0.06 - 0.4 (30-22)
58372-1	Head only for, AMP CT 2.0	2 to 28 ways
58063-2	Head only, for AMPLIMITE HDE - 20	0.05 - 0.6 (30-20)
58246-1	Head only, for MTA 100	0.06 - 0.4 (30-22)
58247-1	Head only, for MTA 156	0.15 - 1.0 (26-18)
937317-1	Mini CT MT	2 to 20 Posns

All options not always listed, please use our online search by terminal PN (where appropriate) to minimise cross-referencing errors, and contact us where information is unclear or missing as there may well be something available for your application.

Pistol Grip III

169756-1- Base Tool without Head Order Handle and Head separately Ideal for small batch production and repair

Image representative of type only

Features:

Interchangeable Heads Complete cycle ratchect control Product automatically indexes after insertion



Part Number	Description	mm² (AWG) or other
734043-1	Complete Tool for HE 13/14 (180°)	0.08 - 0.22 (28-24)
734041-1	Complete Tool for HE-13/14 (90°)	0.08 - 0.22 (28-24)
734042-1	Head only for HE-13/14 (180°)	0.08 - 0.22 (28-24)
734040-1	Head only for HE-13/14 (90°)	0.08 - 0.22 (28-24)
870090-1	MT Connector Ribbon cable	2 to 20 Posns

All options not always listed, please use our online search by terminal PN (where appropriate) to minimise cross-referencing errors, and contact us where information is unclear or missing as there may well be something available for your application.

549033-1 - complete tool

Features:

Suitable for low volume production and repair work.

The connector housing is placed in a support frame and the handles are partially closed, then the wire can be inserted up against the wire stop.

Completely closing the handles pushes the wires into the IDC contacts and completes the terrnination.



Revised:

Hand Tool - ANSLEY 779-2100

1437000-6 for all STD DIP Plugs

Features:

One Stationary Handle
One Moveable Handle
Upper Platten
Lower Platten mounting Plate
Accepts a range of Lower Platten Blocks to crimp a wide variety
of products




Image representative of type only

Part Number	Description	mm² (AWG) or other
1-1437000-2	Platten Block - ANSLEY 609 /622 Ribbon Cable Socket Connectors Use in Hand Tool 1437000-6	10 to 60 Pos
1437000-8	Platten Block - ANSLEY 609 Ribbon Cable Socket Connectors Use in Hand Tool 1437000-6	10 to 64 Pos
1437000-9	Platten Block - ANSLEY 622 Ribbon Cable Socket Connectors Use in Hand Tool 1437000-6	10 to 64 Pos
1-1437000-3	Platten Block - ANSLEY 622 Ribbon Cable Socket Connectors Use in Hand Tool 1437000-6	10 to 60 Pos

All options not always listed, please use our online search by terminal PN (where appropriate) to minimise cross-referencing errors, and contact us where information is unclear or missing as there may well be something available for your application.