

1825203-4 Product Details

Have a Question?

Chat with a Product Information Specialist



1825203-4

TE Internal Number: 1825203-4

Active

Slide Switches

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

Product Highlights:

- 3 Positions
- Four Pole - Three Throw Configuration (Pole-Throw)
- Actuator Style = Extended, Side
- Actuator Color = Black
- MSSA Series

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [SLIDE SWITCH, 3 POS. \(MSSA-3350R SERIES\)](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Four Pole - Three Throw
- Actuator Style = Extended, Side
- Mount Angle = Vertical
- Terminal Configuration = Standard
- Grade = Instrumentation
- Termination Type = PC
- PCB Mount Retention = With

Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

Body Related Features:

- [Number of Positions](#) = 3
- Actuator Color = Black
- Series = MSSA
- Mount Style = Through-Hole
- PCB Tail Length (mm [in]) = 3.51 [0.136]
- PCB Mount Retention Type = Guide Posts
- Actuator Length (mm [in]) = 9.02 [0.355]
- Actuator Material = Polyester
- Actuator Travel = 2.50 [.098]

Contact Related Features:

- Contact Plating = Gold

Housing Related Features:

- UL Flammability Rating = UL 94V-0

Configuration Related Features:

- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Stamped Marking = With

Other:

- Brand = Alcoswitch

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

