

Catalog

- ▶ [Home](#)
- ▶ [Part Number Search](#)
- ▶ [Document Search](#)
- ▶ [CAD Model Search](#)
- ▶ [Text Search](#)
- ▶ [Alternate/Lead Free Part Search](#)
- ▶ [Multiple Part Comparison](#)
- ▶ [Alphabetical Search](#)
- ▶ [Brand Search](#)
- ▶ [Industry Product Search](#)
- ▶ [Product Type Search](#)
- ▶ [Product Family Search](#)
- ▶ [Competitor Cross Reference](#)
- ▶ [Lead Free Solutions](#)
- ▶ [Tool Search](#)
- ▶ [Help/Glossary](#)

CPC (Circular Plastic) & Metal-Shell CPC Connectors

↳ CPC Accessories

AMP 182655-1  [Active](#) [Not Reviewed for ELV/RoHS Compliance](#)

(Tyco Electronics P/N:
182655-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ✦ General Info ✦ Sales Info ✦ Assembly Subcontractors 	<ul style="list-style-type: none"> ✦ Pricing ✦ Product Availability 	<ul style="list-style-type: none"> ✦ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Usage](#)

[Product Usage](#)

[Product Usage](#)

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	Not reviewed for compliance
Product Type:	Cable Clamp
Shell Size:	17
Body Style:	Straight
Cable Diameter (Max.) (mm [in]):	11.51 [0.453]
Cable Clamp Material:	Thermoplastic
Packaging Method:	Individual
Cover:	Without

Other Properties:

Thread Size:	15/16 - 20 UNEF-2B
Cable Clamp Flammability Rating:	UL94V-0
Packaging Quantity:	25

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)