






Wednesday, May 09, 2007

183040-1 Product Details

 <p>183040-1</p> <p> Active</p>	<p>CPC Connectors</p> <p> Always EU RoHS/ELV Compliant (Statement of Compliance)</p> <p>Product Highlights:</p> <ul style="list-style-type: none"> ● Connector ● Number of Positions = 14 ● Receptacle ● For Use With Pin Contacts ● Not Preloaded <p>View all Features</p>	<p>Quick Links</p> <ul style="list-style-type: none"> ▶ Check Pricing & Availability ▶ Search for Tooling ▶ Product Feature Selector ▶ Contact Us About This Product 		
<p>Documentation & Additional Information</p> <table border="1"> <tr> <td data-bbox="316 618 938 1003"> <p>Product Drawings:</p> <ul style="list-style-type: none"> ● C.P.C square flange rec. for pin ctcs., size 17-16 (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> ● None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> ● None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> ● None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> ● None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> ● 3D Model (STEP, Version A) ● 3D Model (IGES, Version A) ● 2D Drawing (DXF, Version A) <p style="text-align: right;">List all Documents</p> </td> <td data-bbox="944 618 1262 1003"> <p>Additional Information:</p> <ul style="list-style-type: none"> ● Product Line Information <p>Additional Product Images:</p> <ul style="list-style-type: none"> ● Contact Arrangement ● Recommended Panel Cutout ● Front View <p>Related Products:</p> <ul style="list-style-type: none"> ● Tooling </td> </tr> </table>			<p>Product Drawings:</p> <ul style="list-style-type: none"> ● C.P.C square flange rec. for pin ctcs., size 17-16 (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> ● None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> ● None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> ● None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> ● None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> ● 3D Model (STEP, Version A) ● 3D Model (IGES, Version A) ● 2D Drawing (DXF, Version A) <p style="text-align: right;">List all Documents</p>	<p>Additional Information:</p> <ul style="list-style-type: none"> ● Product Line Information <p>Additional Product Images:</p> <ul style="list-style-type: none"> ● Contact Arrangement ● Recommended Panel Cutout ● Front View <p>Related Products:</p> <ul style="list-style-type: none"> ● Tooling
<p>Product Drawings:</p> <ul style="list-style-type: none"> ● C.P.C square flange rec. for pin ctcs., size 17-16 (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> ● None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> ● None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> ● None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> ● None Available <p>CAD Files: (CAD Format & Compression Information)</p> <ul style="list-style-type: none"> ● 3D Model (STEP, Version A) ● 3D Model (IGES, Version A) ● 2D Drawing (DXF, Version A) <p style="text-align: right;">List all Documents</p>	<p>Additional Information:</p> <ul style="list-style-type: none"> ● Product Line Information <p>Additional Product Images:</p> <ul style="list-style-type: none"> ● Contact Arrangement ● Recommended Panel Cutout ● Front View <p>Related Products:</p> <ul style="list-style-type: none"> ● Tooling 			
<p>Product Features (Please use the Product Drawing for all design activity)</p> <table border="1"> <tr> <td data-bbox="316 1055 794 1503"> <p>Product Type Features:</p> <ul style="list-style-type: none"> ● Product Type = Connector ● Number of Positions = 14 ● Gender = Receptacle ● For Use With = Pin Contacts ● Termination Style = Wire ● Shell Size = 17 ● Shell Type = All Plastic ● Product Series = Series 1 ● Thread Size = 15/16-20 UNEF-2A ● Sealed = No ● Insulation Diameter (mm [in]) = 2.54 [0.100] ● CSA Certified = Yes <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> ● Preloaded = No ● VDE Tested = No ● Panel Attachment Method = Square Flange <p>Body Related Features:</p> <ul style="list-style-type: none"> ● Mount Style = Panel ● UL Rating = Recognized </td> <td data-bbox="801 1055 1262 1503"> <p>Contact Related Features:</p> <ul style="list-style-type: none"> ● Standard or Reverse Gender = Standard <p>Housing Related Features:</p> <ul style="list-style-type: none"> ● Housing Material = Thermoplastic ● Housing Color = Black ● Housing Flammability Rating = UL 94V-0 <p>Configuration Related Features:</p> <ul style="list-style-type: none"> ● Reverse Numbering = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> ● RoHS/ELV Compliance = RoHS compliant, ELV compliant ● Lead Free Solder Processes = Not relevant for lead free process ● RoHS/ELV Compliance History = Always was RoHS compliant <p>Packaging Related Features:</p> <ul style="list-style-type: none"> ● Packaging Quantity = 25 <p>Other:</p> <ul style="list-style-type: none"> ● Brand = AMP </td> </tr> </table>			<p>Product Type Features:</p> <ul style="list-style-type: none"> ● Product Type = Connector ● Number of Positions = 14 ● Gender = Receptacle ● For Use With = Pin Contacts ● Termination Style = Wire ● Shell Size = 17 ● Shell Type = All Plastic ● Product Series = Series 1 ● Thread Size = 15/16-20 UNEF-2A ● Sealed = No ● Insulation Diameter (mm [in]) = 2.54 [0.100] ● CSA Certified = Yes <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> ● Preloaded = No ● VDE Tested = No ● Panel Attachment Method = Square Flange <p>Body Related Features:</p> <ul style="list-style-type: none"> ● Mount Style = Panel ● UL Rating = Recognized 	<p>Contact Related Features:</p> <ul style="list-style-type: none"> ● Standard or Reverse Gender = Standard <p>Housing Related Features:</p> <ul style="list-style-type: none"> ● Housing Material = Thermoplastic ● Housing Color = Black ● Housing Flammability Rating = UL 94V-0 <p>Configuration Related Features:</p> <ul style="list-style-type: none"> ● Reverse Numbering = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> ● RoHS/ELV Compliance = RoHS compliant, ELV compliant ● Lead Free Solder Processes = Not relevant for lead free process ● RoHS/ELV Compliance History = Always was RoHS compliant <p>Packaging Related Features:</p> <ul style="list-style-type: none"> ● Packaging Quantity = 25 <p>Other:</p> <ul style="list-style-type: none"> ● Brand = AMP
<p>Product Type Features:</p> <ul style="list-style-type: none"> ● Product Type = Connector ● Number of Positions = 14 ● Gender = Receptacle ● For Use With = Pin Contacts ● Termination Style = Wire ● Shell Size = 17 ● Shell Type = All Plastic ● Product Series = Series 1 ● Thread Size = 15/16-20 UNEF-2A ● Sealed = No ● Insulation Diameter (mm [in]) = 2.54 [0.100] ● CSA Certified = Yes <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> ● Preloaded = No ● VDE Tested = No ● Panel Attachment Method = Square Flange <p>Body Related Features:</p> <ul style="list-style-type: none"> ● Mount Style = Panel ● UL Rating = Recognized 	<p>Contact Related Features:</p> <ul style="list-style-type: none"> ● Standard or Reverse Gender = Standard <p>Housing Related Features:</p> <ul style="list-style-type: none"> ● Housing Material = Thermoplastic ● Housing Color = Black ● Housing Flammability Rating = UL 94V-0 <p>Configuration Related Features:</p> <ul style="list-style-type: none"> ● Reverse Numbering = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> ● RoHS/ELV Compliance = RoHS compliant, ELV compliant ● Lead Free Solder Processes = Not relevant for lead free process ● RoHS/ELV Compliance History = Always was RoHS compliant <p>Packaging Related Features:</p> <ul style="list-style-type: none"> ● Packaging Quantity = 25 <p>Other:</p> <ul style="list-style-type: none"> ● Brand = AMP 			

Languages: English | [Deutsch](#) | [Español](#) | [Português \(do Brasil\)](#) | [Русский](#) | [Italiano](#) | [正體中文 \(繁體\)](#) | [中文 \(简体\)](#) | [日本語](#)
 Country Sites: [China](#) | [Japan](#)

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Supplier](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)
 © 2007 Tyco Electronics Corporation All Rights Reserved