

Product Details for 183075 - 1



183075 - 1

[Active](#)

CPC Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Connector
- ? Number of Positions = 24
- ? Receptacle
- ? Used With Pin Contacts
- ? Not Preloaded

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [C.P.C square flange size 23 -24 std. sex series 1](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Circular Plastic Connector With Type III+ Contacts](#) (PDF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version A2)
- ? [3D Model](#) (IGES, Version A2)
- ? [2D Drawing](#) (DXF, Version A2)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Contact Arrangement](#)
- ? [Keying Options](#)
- ? [Recommended Panel Cutout](#)
- ? [Front View](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Number of Positions](#) = 24
- ? [Gender](#) = Receptacle
- ? [Shell Size](#) = 23
- ? [Shell Type](#) = All Plastic
- ? [Product Series](#) = Series 1
- ? [Sealed](#) = No
- ? CSA Certified = Yes

Mechanical Attachment:

- ? [Preloaded](#) = No
- ? [VDE Tested](#) = No
- ? Panel Attachment Method = Square Flange
- ? Keying = A

Termination Related Features:

- ? [Shell Thread Size](#) = 1 -3/8 - 18 UNEF -2A

Body Related Features:

- ? Used With = Pin Contacts
- ? [Mount Style](#) = Mounting Holes
- ? UL Rating = Recognized

Contact Related Features:

- ? [Standard or Reverse Gender](#) = Standard

Housing Related Features:

- ? Housing Material = Thermoplastic
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -0

Configuration Related Features:

- ? [Reverse Numbering](#) = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Wire

Other:

- ? Brand = AMP