

Product Details for 183082 - 1



183082 - 1

[Active](#)

CPC Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Connector
- ? Number of Positions = 3
- ? Plug
- ? Used With Socket Contacts
- ? Not Preloaded

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [C.P.C. PLUG ASS'Y SIZE 17 -3 STD SEX SERIES 3](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version A)
- ? [3D Model](#) (IGES, Version A)
- ? [2D Drawing](#) (DXF, Version A)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Contact Arrangement](#)

Related Products:

- ? [Tooling](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Number of Positions](#) = 3
- ? [Gender](#) = Plug
- ? [Shell Size](#) = 17
- ? [Shell Type](#) = All Plastic
- ? [Product Series](#) = Series 3
- ? [Sealed](#) = No
- ? Wire Insulation Diameter (mm [in]) = 5.59 [0.220]

Mechanical Attachment:

- ? [Preloaded](#) = No
- ? [VDE Tested](#) = No

Termination Related Features:

- ? [Shell Thread Size](#) = 15/16 -20 UNEF -2A

Body Related Features:

- ? Used With = Socket Contacts
- ? [Mount Style](#) = Free Hanging

Contact Related Features:

- ? [Standard or Reverse Gender](#) = Standard

Housing Related Features:

- ? Housing Material = Thermoplastic
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -0

Configuration Related Features:

- ? [Reverse Numbering](#) = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Wire

Other:

- ? Brand = AMP