



[+ TERMINALS & SPLICES](#)
[RINGS & SPADES](#)



✓ Active

TE CONNECTIVITY (TE)

TERMINAL,SOLIS R 8 10MM

SOLISTRAND

184064-1

TE Internal Number: 184064-1

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Terminal Type Ring Tongue

Stud Diameter (mm) 10, 10.5

Stud Diameter (in) .413

Tongue Thickness 1.22 mm [.048 in]

Wire Size (AWG) 8

Wire Size (mm²) 8

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

TERMINAL, RING TONGUE,SOLISTRAND(TM)

PDF (TIFF AVAILABLE)

English

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

Agency Approvals

UL Report

WIRE CONN, TERMINALS, BUTT AND PARALLEL CONNECTORS-PLASTI-GRIP, SOLISTRAND, STD B, DIAMOND GRIP, PIDG AND AMPOWER REPORT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Sealable No

Barrel Type Closed Barrel

Wire/Cable Type Regular Wire

Insulated No

Insulated Wire Support No

Shape Code RING-054

Wire/Cable Composition Solid or Stranded

Configuration Features

Number of Holes 1

Body Features

Plating Material Copper, Tin

Inspection Slot No

Contact Features

Terminal Type Ring Tongue

Terminal Orientation Straight

Dimensions

Stud Diameter (mm) 10, 10.5

Stud Diameter (in) .413

Tongue Thickness 1.22 mm [.048 in]

Wire Size (AWG) 8

Wire Size (mm²) 8

Wire Size (CMA) 13100 – 20800

Overall Length (mm) 29.6

Operation/Application

Heavy Duty No

Industry Standards

Government Qualified No

Packaging Features

Packaging Method Box

Packaging Quantity 100

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
