


Catalog

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Terminals and Splices**↳ Splices - Closed Barrel**
AMP **320559**  [Active](#)
**Directive 2002/95/EC
Compliant**
[RoHS Compliant](#)**(Tyco Electronics P/N: 320559)**[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ✦ General Info ✦ Sales Info ✦ Assembly Subcontractors 	<ul style="list-style-type: none"> ✦ Pricing ✦ Product Availability 	<ul style="list-style-type: none"> ✦ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)**Searchable Features:**

Brand:	AMP
Government/Industry Qualification:	Yes
Government/Industry Part Number:	M7928/5-3, AS7928/5-3
Product Type:	Splice
Sealed:	No
Class:	1 & 2
Splice Type:	Butt
Butt Splice Type:	Standard
Body Style:	PIDG
Insulation:	Yes

Other Properties:

Insulation Sleeve Material:	Nylon
Packaging Quantity:	50
Comment:	22-16 splices are 22-18 range in accordance with MIL-T-7928.

Insulation Support:	Insulation Support
Insulation Diameter (mm [in]):	3.18 [.125] Max.
Wire Range (mm [AWG]):	0.26-1.65 ² [22-16]
Wire Range (CMA):	509 – 3,260
Material:	Copper
Finish:	Tin
Packaging Method:	Loose Piece
Color:	Red

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)