


## 499997-9 Product Details

[Live Product Chat](#)

499997-9

### Ribbon Cable Connectors (AMP-LATCH)

[Not EU RoHS or ELV Compliant \(Find RoHS Compliant Alternates\)](#)

#### Product Highlights:

- Connector Type = NOVO
- 40 Positions
- Receptacle
- Mating Polarization Type = Military
- With Mating Polarization

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

TE Internal Number: 499997-9



Superseded

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)[Search for Replacement Parts](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- [PERSONAL SYSTEMS PRODUCTS](#) (PDF, English)

#### Product Specifications:

- [Connector, Flat Cable Round Conductor, AMP-LATCH Nov...](#) (PDF, English)

#### Application Specifications:

- [AMP-LATCH Novo Receptacles for Ribbon Cable with Con...](#) (PDF, English)

#### Instruction Sheets:

- [Connector-Specific Kit f/AMP-LATCH Standard and Novo...](#) (PDF, English)

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Connector Type](#) = NOVO
- [Number of Positions](#) = 40
- Gender = Receptacle
- [Mating Polarization Type](#) = Military
- [Mating Polarization](#) = With
- [Mounting Ears](#) = Without
- PCB Retention Feature = No
- Mating Connector Lock = Without
- Strain Relief = Without
- With Cover Preassembled = Yes
- Comment = Receptacle can be used in applications requiring non-polarization, as well as military polarization.

#### Termination Related Features:

- [Solder Tail Contact Plating](#) = Tin-Lead

#### Body Related Features:

- Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]

#### Contact Related Features:

- [Contact Plating, Mating Area, Material](#) = Gold (15)
- Contact Base Material = Phosphor Bronze

#### Housing Related Features:

- [Housing Color](#) = Black
- Housing Material = Thermoplastic
- Housing Flammability Rating = UL 94V-0

#### Configuration Related Features:

- Cable Stop = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Conditions for Usage:

- [Terminate To](#) = Ribbon Cable

#### Other:

- Brand = AMP

[Provide Website Feedback](#) | [Need Help?](#)