


DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 19
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

		REVISIONS				
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	✓		E	REDRAWN-REV. PER G-1478, G-1175 & P85-0101, -0102, -0103, -0106	11/21/86	Pjm
✓	✓		F	OBSOLETE - 58-7 PER G-2393	2/21/87	SS Pjm
✓	✓		G	REVISED G-3062	4-12-88	725/64
✓	✓		H	OBS-4-6 PER G-3795 & G-3796	11/14/88	AG
✓	✓		J	REV PER G-5282	11/27/88	212/205
✓	✓		K	REV/0720-3049-93	15-18-95	TD/MLA



- 1 WIRE INSULATION DIA. = SEE TABLE, DIM. "A"
- 2 TONGUE MATERIAL THK. = .031 ± .002
- 3 BODY FINISH: TIN PLATE (MIL-T-10727) .000100 MIN THK.

DIM "A"	QUANTITY	DESCRIPTION	PART NO
.115-.170	100	LOOSE PC, BOX	8-52936-1
.115-.182	100	ON TAPE, SM. BOX	52936-1
.117-.182	1000	ON TAPE, LG. BOX	52936-2
.115-.170	100	ON TAPE, SM. BOX	52936-1
.115-.170	1000	ON TAPE, LG. BOX	52936-1
.115-.182	5000	ON TAPE, REEL	52936-3
.115-.182	—	LOOSE PIECE	52936-2
.115-.170	5000	ON TAPE, REEL	52936-1
.115-.170	—	LOOSE PIECE	52936

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .003 ANGLES ±	CONTRACT NO		AMP INCORPORATED Harrisburg, Pa.
	OR UTA/RFB 9-27-85		
MATERIAL INSULATION: NYLON-BLUE SLEEVE: COPPER (QG-C-576) BODY: PHOSPHOR BRONZE (QG-B-750)	CHK	11/27/86	NAME TERMINAL, P.I.D.G., SPRING SPADE (SHORT) WIRE SIZE: 16-14
	APPD	11/27/86	
	DSGN APPD		SIZE B
	OTHER APPD		FSCM NO 00779
			DRAWING NO 52936
			SCALE NTS
			SHEET 1 OF 1