


**Product Details for 5352132 - 1**



**5352132 - 1**

[Active](#)

**2mm Hard Metric PCB Mount Connectors  
(Z - PACK 2mm HM)**

[RoHS Compliant \(Statement of Compliance\)](#)

**Product Highlights:**

- ? Connector
- ? Connector Type = Type B, 22 Column
- ? Plug
- ? Interface Type = 2mm HM
- ? Contact Type = ACTION PIN Post

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(1\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [MALE ASSEMBLY, Z - PACK 2mm HM, TYPE B](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? None Available

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)
- ? [Mating Products \(1\)](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Connector
- ? Connector Type = Type B, 22 Column
- ? [Gender](#) = Plug
- ? [Number of Positions](#) = 110
- ? [PCB Mount Angle](#) = Vertical
- ? [Mating Polarization](#) = Without
- ? [Shielded](#) = No

**Mechanical Attachment:**

- ? [Board Mount](#) = Free Board
- ? Module Length (mm [in]) = 43.88 [1.729]
- ? [Crosstalk Version](#) = Standard

**Termination Related Features:**

- ? [Interface Type](#) = 2mm HM
- ? Termination End Plating = Tin over Nickel

**Body Related Features:**

- ? [Number of Rows](#) = 5
- ? [Grounding Contact](#) = Without

**Contact Related Features:**

- ? Contact Type = ACTION PIN Post, Signal
- ? [Feedthrough Post Length \(mm \[in\]\)](#) = 3.71 [0.146]
- ? [CompactPCI](#) = No
- ? [Contact Mating Area Plating](#) = Gold over Nickel
- ? Contact Style = Short Tail
- ? Feedthrough Post Length (Rows A - E) (mm [in]) = 9.70 [0.382]
- ? Contact Material = Phosphor Bronze

**Housing Related Features:**

- ? Housing Material = Glass - Filled Polyester
- ? Housing Color = Gray
- ? Housing Flammability Rating = UL 94V -0

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

**Other:**

- ? Brand = AMP