


## Product Details for 603324 - 1



**603324 - 1**

[Active](#)

### Heat Shrink Tubing

[RoHS Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- ? Jacket Tubing
- ? General Purpose Application
- ? Operating Temperature = -30 - 125 °C
- ? Inside Diameter (Min -Max) = 1.57 - 3.18 mm
- ? Without Sealant

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [AMPSULATION VFP21 AND FP21](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? [Heat Shrink Tubing](#) (PDF, English)

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Jacket Tubing
- ? [Sealant](#) = Without
- ? Style = VFP21
- ? Size = 3.18 [.125]
- ? Color = Black
- ? Material = Polyolefin
- ? Proprietary Name = AMPSULATION

#### Body Related Features:

- ? [Marked](#) = Yes
- ? [Shrink Ratio](#) = 2:1
- ? [Wall Style](#) = Thin
- ? [Wall Thickness - Full Recovery \(Nominal\) \(mm \[in\]\)](#) = 0.51 [0.020]
- ? [Length \(M \[ft\]\)](#) = 1.219 [3.99]
- ? Marking Color = White

#### Housing Related Features:

- ? [Inside Diameter \(Min -Max\) \(mm \[in\]\)](#) = 1.57 - 3.18 [0.062 - 0.125]

#### Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? Operating Temperature (°C) = -30 - +125

#### Operation/Application:

- ? Application = General Purpose

#### Packaging Related Features:

- ? Packaging Method = Bag
- ? Weight per Linear Foot (g [lb]) = 1.089 [0.0024]

#### Other:

- ? Brand = AMP