

## Product Details for 608507 -5

### Heat Shrink Tubing

[RoHS Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- ? Jacket Tubing
- ? Military Application
- ? Operating Temperature = -55 - 110 °C
- ? Inside Diameter (Min -Max) = 12.70 - 38.10 mm
- ? With Sealant

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

No Image Available

**608507 -5**

 [Active](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [TUBING, HEAT SHRINK, AMPSULATION, MHWP31, 1.50 DIA](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Jacket Tubing
- ? [Sealant](#) = With
- ? Style = MHWP31
- ? Size = 38.10 [1.501]
- ? Color = Black
- ? Material = Polyolefin
- ? Proprietary Name = AMPSULATION

#### Body Related Features:

- ? Sealant Type = Thermoplastic (Hotmelt)
- ? [Marked](#) = Yes
- ? [Shrink Ratio](#) = 3:1
- ? [Wall Style](#) = Heavy
- ? [Wall Thickness - Full Recovery \(Nominal\) \(mm \[in\]\)](#) = 3.56 [0.140]
- ? [Length \(M \[ft\]\)](#) = 0.305 [1.00]
- ? Marking Color = Yellow

#### Contact Related Features:

- ? Approved Standards = MIL I 23053

#### Housing Related Features:

- ? [Inside Diameter \(Min -Max\) \(mm \[in\]\)](#) = 12.70 - 38.10 [0.500 - 1.500]

#### Industry Standards:

- ? Government/Industry Qualification = Yes
- ? Government/Industry Part Number = M23053/15 -103 -0
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- ? Operating Temperature (°C) = -55 - +110

#### Operation/Application:

- ? Application = Military

#### Packaging Related Features:

- ? Packaging Method = Bag
- ? Weight per Linear Foot (g [lb]) = 81.60 [0.180]

#### Other:

- ? Brand = AMP