

1-1337433-0 Product Details

Have a Question?

Chat with a Product Information Specialist



1-1337433-0

BNC RF Connectors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector - RF
- Jack
- Connector Style = Jack
- Applies To Coaxial Cable
- Coaxial Cable Termination Type = Crimp

[View all Features](#)

TE Internal Number: 1-1337433-0

[Active](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [BNC BULKHEAD JACK REAR MOUNT CRIMP 50 OHM RG58C/U, 1...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector - RF
- Gender = Jack
- [Crimp Type](#) = Hex
- Body Style = Bulkhead
- [Grade](#) = Professional
- [Body Material](#) = Brass
- [Sealed](#) = No
- [Isolated](#) = No
- [Dielectric Material](#) = PTFE
- Number of Ports = 1
- Panel Thickness (mm [in]) = 2.00 - 5.00 [0.078 - 0.197]
- Flats Dimension = 16.0 A/F
- Gasket Material = White Silicone Rubber

Mechanical Attachment:

- Surface Mountable = No
- [Panel Attachment](#) = With
- Panel Attachment Method = Hex Nut
- Panel Attachment Style = Rear Mount
- Panel Cutout = 12.0mm x 12.9mm D-Shape
- Flange Dimension [A/F] (mm [in]) = 17.5 [0.689]
- Flange and Thread Material = Brass
- Lockwasher Material = Mild Steel
- Lockwasher Plating = Nickel

Electrical Characteristics:

- [Connector Impedance \(Ω\)](#) = 50
- Frequency = DC - 4 GHz

Termination Related Features:

- [Coaxial Cable Termination Type](#) = Crimp

Body Related Features:

- [Hardware Included](#) = No
- [Body Plating](#) = Nickel
- [Polarized](#) = No
- Ferrule Type = Hex
- Hand Tool No. = 9-1478240-0
- Interchangeable Die Set Number = 9-1478242-0
- Crimp Dimensions = 1.75 + 2.6 + 5.6 + 6.5

Contact Related Features:

- [Center Contact Material](#) = Brass
- [Center Contact Plating](#) = Gold

Housing Related Features:

- Connector Style = Jack

Configuration Related Features:

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 141A, 58C, Raychem 5021D1331, Raychem 5021D1831, Raychem 5021M1631, Raychem EPD 71169Q, URM 43, URM 76

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- [Applies To](#) = Coaxial Cable
- Military Style Number = UG-1804/U
- Operating Temperature (Max.) (°C) = 165

Packaging Related Features:

- Packaging Method = Individual
- Packaging Quantity = 50

Other:

- Brand = Greenpar

BOOKMARK

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

