

## 1-1337436-0 Product Details

**Have a Question?**

Chat with a Product Information Specialist



1-1337436-0

### BNC RF Connectors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

**Product Highlights:**

- Connector - RF
- Jack
- Connector Style = Jack
- Applies To Coaxial Cable
- Coaxial Cable Termination Type = Crimp

[View all Features](#)

TE Internal Number: 1-1337436-0

[Active](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

**Product Drawings:**

- [BNC BULKHEAD JACK REAR MOUNT CRIMP 75 OHM RG59B/U, 6...](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- None Available

**Product Specifications:**

- None Available

**Application Specifications:**

- None Available

**Instruction Sheets:**

- None Available

**CAD Files:**

- None Available

**Additional Information:**

- [Product Line Information](#)

**Related Products:**

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

**Product Type Features:**

- [Product Type](#) = Connector - RF
- Gender = Jack
- [Crimp Type](#) = Hex
- Body Style = Bulkhead
- [Grade](#) = Professional
- [Body Material](#) = Brass
- [Sealed](#) = No
- [Isolated](#) = No
- [Dielectric Material](#) = PTFE
- Number of Ports = 1
- Panel Thickness (mm [in]) = 2.00 - 5.00 [0.078 - 0.197]
- Flats Dimension = 16.0 A/F
- Gasket Material = White Silicone Rubber

**Mechanical Attachment:**

- Surface Mountable = No
- [Panel Attachment](#) = With
- Panel Attachment Method = Hex Nut
- Panel Attachment Style = Rear Mount
- Panel Cutout = 12.0mm x 12.9mm D-Shape
- Flange Dimension [A/F] (mm [in]) = 17.5 [0.689]
- Flange and Thread Material = Brass
- Lockwasher Material = Mild Steel
- Lockwasher Plating = Silver

**Electrical Characteristics:**

- [Connector Impedance \(Ω\)](#) = 75
- Frequency = DC - 2 GHz

**Termination Related Features:**

- [Coaxial Cable Termination Type](#) = Crimp

**Body Related Features:**

- [Hardware Included](#) = No
- [Body Plating](#) = Silver
- [Polarized](#) = No
- Ferrule Type = Hex
- Hand Tool No. = 9-1478240-0
- Interchangeable Die Set Number = 9-1478242-0
- Crimp Dimensions = 1.75 + 2.6 + 5.6 + 6.5

**Contact Related Features:**

- [Center Contact Material](#) = Brass
- [Center Contact Plating](#) = Silver

**Housing Related Features:**

- Connector Style = Jack

**Configuration Related Features:**

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 140, 210, 59B, 62A, Raychem 9524A1311, Raychem 9524A1811, URM 90

**Industry Standards:**

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

**Conditions for Usage:**

- [Applies To](#) = Coaxial Cable
- Military Style Number = UG-1808/U
- Operating Temperature (Max.) (°C) = 165

**Packaging Related Features:**

- Packaging Method = Individual
- Packaging Quantity = 50

**Other:**

- Brand = Greenpar

BOOKMARK

### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

